

# FLKM-D15 SUB/B/ZFKDS - Termination board



2304047

<https://www.phoenixcontact.com/us/products/2304047>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Standard 1:1 D-SUB module, with spring-cage connection and D-SUB socket strip, no. of positions 15

The figure shows the version FLKM-D37 SUB/S/ZFKDS

## Your advantages

- 9-pos. ... 50-pos.
- Spring-cage connection technology
- In accordance with IEC 60807-2
- 1:1 connection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2304047       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C422          |
| Product key                          | DK2182        |
| GTIN                                 | 4017918944018 |
| Weight per piece (including packing) | 97.61 g       |
| Weight per piece (excluding packing) | 69.07 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Interface module |
| Number of positions | 15               |

#### Insulation characteristics: Air clearances and creepage distances

|                      |                       |
|----------------------|-----------------------|
| Insulation           | Functional insulation |
| Overvoltage category | II                    |
| Pollution degree     | 2                     |

### Electrical properties

|                         |           |
|-------------------------|-----------|
| Operating voltage (AC)  | ≤ 30 V AC |
| Operating voltage (DC)  | ≤ 60 V DC |
| Current (per branch)    | ≤ 2.5 A   |
| Current (Total current) | ≤ 37.5 A  |

#### Air clearances and creepage distances

|                          |                    |
|--------------------------|--------------------|
| Rated insulation voltage | 125 V              |
| Rated surge voltage      | 1.2 kV (1.2/50 μs) |

### Connection data

#### Connection 1 (control level)

|                                  |                    |
|----------------------------------|--------------------|
| Connection in acc. with standard | IEC 60807-2        |
| Connection method                | D-SUB socket strip |
| Screw thread                     | UNC 4-40           |
| Number of connections            | 1                  |
| Number of positions              | 15                 |
| Insertion/withdrawal cycles      | > 500              |
| Pitch                            | 2.74 mm            |

#### Connection 2 (field level)

|                                  |   |
|----------------------------------|---|
| Connection method                | Spring-cage connection  |
| Stripping length                 | 7 mm  |
| Number of positions              | 16  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                     |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                   |
|                                  | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Ferrule without plastic sleeve) |
|                                  | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)    |
| Conductor cross-section AWG      | 24 ... 12   |
| Pitch                            | 5.08 mm   |

### Signaling

|                |    |
|----------------|----|
| Status display | no |
|----------------|----|

# FLKM-D15 SUB/B/ZFKDS - Termination board



2304047

<https://www.phoenixcontact.com/us/products/2304047>

|                        |    |
|------------------------|----|
| Status display present | no |
|------------------------|----|

## Dimensions

### Item dimensions

|        |          |
|--------|----------|
| Width  | 45 mm    |
| Height | 77 mm    |
| Depth  | 51.27 mm |

## Material specifications

|                             |                  |
|-----------------------------|------------------|
| Color                       | green (RAL 6021) |
| Housing insulation material | PVC              |

## Environmental and real-life conditions

### Ambient conditions

|  |                  |
|--|------------------|
| Degree of protection (Module)                | IP20             |
| Degree of protection (Installation location) | ≥ IP54           |
| Ambient temperature (operation)              | -20 °C ... 50 °C |
| Ambient temperature (storage/transport)      | -20 °C ... 70 °C |
| Altitude                                     | ≤ 2000 m         |

## Approvals

### UKCA

|             |                |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

## Standards and regulations

### Air clearances and creepage distances

|                       |                |
|-----------------------|----------------|
| Standards/regulations | EN IEC 60664-1 |
|-----------------------|----------------|

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

# FLKM-D15 SUB/B/ZFKDS - Termination board



2304047

<https://www.phoenixcontact.com/us/products/2304047>

## Drawings

Circuit diagram



# FLKM-D15 SUB/B/ZFKDS - Termination board





2304047

<https://www.phoenixcontact.com/us/products/2304047>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2304047>

|  <b>cUL Recognized</b><br>Approval ID: E238705 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 125 V                 | 2.5 A                 | -                 | -                           |

|  <b>UL Recognized</b><br>Approval ID: E238705 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 125 V                 | 2.5 A                 | -                 | -                           |

# FLKM-D15 SUB/B/ZFKDS - Termination board



2304047

<https://www.phoenixcontact.com/us/products/2304047>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002780 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FLKM-D15 SUB/B/ZFKDS - Termination board



2304047

<https://www.phoenixcontact.com/us/products/2304047>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)