

UM-BASIC/PRO PE CONTACT L2 - Functional ground contact



2202026

<https://www.phoenixcontact.com/us/products/2202026>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 2

The figure shows the versions for PCB level 1

Your advantages

- Different base profiles, each with three PCB levels
- Module covers of different geometries can be positioned in any way
- Compatibility with many standard connection technologies
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2202026 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | AC13 |
| Product key | ACHDAC |
| GTIN | 4055626005379 |
| Weight per piece (including packing) | 2.6 g |
| Weight per piece (excluding packing) | 2.612 g |
| Customs tariff number | 73269098 |
| Country of origin | DE |

UM-BASIC/PRO PE CONTACT L2 - Functional ground contact



2202026

<https://www.phoenixcontact.com/us/products/2202026>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|----------------|------------------------------|
| Product type | Ground contact |
| Housing type | Press-drawn section housings |
| Housing series | UM-BASIC |

Dimensions

| | |
|--------|---------|
| Width | 6 mm |
| Height | 30.6 mm |
| Depth | 20.8 mm |

Material specifications

| | |
|------------------|----------------|
| Color | silver-colored |
| Housing material | Steel |
| Contact material | CuSn |

Mounting

| | |
|---------------------------|--|
| Mounting type | Screw mounting |
| Tightening torque / speed | Mounting the PCB: 0.5 Nm-0.6 Nm / 500 rpm-1000 rpm |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

UM-BASIC/PRO PE CONTACT L2 - Functional ground contact



2202026

<https://www.phoenixcontact.com/us/products/2202026>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-BASIC/PRO PE CONTACT L2 - Functional ground contact



2202026

<https://www.phoenixcontact.com/us/products/2202026>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com