

FLK 20/2FLK14/EZ-DR/ 50/KONFEK - Cable



2305059

<https://www.phoenixcontact.com/us/products/2305059>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (2x 14-position); cable length: 0.5 m

Your advantages

- Suitable for connecting 16-channel digital cards, e.g., SIMATIC® ET 200SP
- The 16 digital signals are split into 2x 8 signals on the field side
- IDC/FLK connector: 20-pos. to two 14-pos. (in accordance with IEC 60603-13)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2305059 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK2215 |
| GTIN | 4046356038898 |
| Weight per piece (including packing) | 58.5 g |
| Weight per piece (excluding packing) | 55.8 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|----------------------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating) |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

Supported controller: EMERSON DeltaV

| | |
|-------------------|--------------|
| Suitable I/O card | VE4001S2T2B5 |
| | VE4002S1T2B6 |

Supported controller: SIEMENS ET 200SP

| | |
|---------------------|---------------------------------------|
| Suitable base unit | 6ES7193-6BP00-0BA0 |
| | 6ES7193-6BP00-2BA0 |
| | 6ES7193-6BP00-0BA1 |
| | 6ES7193-6BP00-0DA0 |
| | 6ES7193-6BP00-2DA0 |
| | 6ES7193-6BP00-0DA1 |
| Suitable I/O module | 6ES7131-6BH01-0BA0 (Base Units A0/A1) |
| | 6ES7131-6BH01-2BA0 (Base Units A0/A1) |
| | 6ES7132-6BH01-0BA0 (Base Units A0/A1) |
| | 6ES7132-6BH01-2BA0 (Base Units A0/A1) |

Cable/line

| | |
|--------------|-------|
| Cable length | 0.5 m |
|--------------|-------|

20X0.14 [PVC]

| | |
|---------------------|-----------|
| UL AWM Style | 2464/1061 |
| Number of positions | 20 |
| Shielded | no |

FLK 20/2FLK14/EZ-DR/ 50/KONFEK - Cable



2305059

<https://www.phoenixcontact.com/us/products/2305059>

| | |
|---|---|
| Cable type | 20X0.14 [PVC] |
| Conductor type | Round cable set |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 20x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 7.60 mm ±0.4 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 64 mm |
| Smallest bending radius, movable installation | 120 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |
| Halogen-free | no |
| Flame resistance | IEC 60332-1-2 (raw cable) |
| | VDE 0842, Part 332-1-2 (raw cable) |
| | IEC 60332-3-22 (raw cable) |
| | UL VW-1 |
| | CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Splitting cable for two modules |

Color code: Single-core wire

| | |
|--------------|-----------------------------------|
| black | IDC/FLK20 (1) = IDC/FLK14-1 (1) |
| brown | IDC/FLK20 (2) = IDC/FLK14-1 (2) |
| red | IDC/FLK20 (3) = IDC/FLK14-1 (3) |
| orange | IDC/FLK20 (4) = IDC/FLK14-1 (4) |
| yellow | IDC/FLK20 (5) = IDC/FLK14-1 (5) |
| green | IDC/FLK20 (6) = IDC/FLK14-1 (6) |
| blue | IDC/FLK20 (7) = IDC/FLK14-1 (7) |
| violet | IDC/FLK20 (8) = IDC/FLK14-1 (8) |
| gray | IDC/FLK20 (9) = IDC/FLK14-2 (1) |
| white | IDC/FLK20 (10) = IDC/FLK14-2 (2) |
| white-black | IDC/FLK20 (11) = IDC/FLK14-2 (3) |
| white-brown | IDC/FLK20 (12) = IDC/FLK14-2 (4) |
| white-red | IDC/FLK20 (13) = IDC/FLK14-2 (5) |
| white-orange | IDC/FLK20 (14) = IDC/FLK14-2 (6) |
| white-yellow | IDC/FLK20 (15) = IDC/FLK14-2 (7) |
| white-green | IDC/FLK20 (16) = IDC/FLK14-2 (8) |
| white-blue | IDC/FLK20 (17) = IDC/FLK14-2 (9) |
| white-violet | IDC/FLK20 (18) = IDC/FLK14-2 (10) |

FLK 20/2FLK14/EZ-DR/ 50/KONFEK - Cable



2305059

<https://www.phoenixcontact.com/us/products/2305059>

| | |
|-------------|-----------------------------------|
| white-gray | IDC/FLK20 (19) = IDC/FLK14-1 (9) |
| brown-black | IDC/FLK20 (20) = IDC/FLK14-1 (10) |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 20 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2


| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 2 |
| Number of positions | 14 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Diagram




Maximum permissible current per path in uncoiled state


2305059


<https://www.phoenixcontact.com/us/products/2305059>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2305059>

| | |
|---|--|
|  | EAC Approval ID: RU*-DE.HB*35.B00385 |
|---|--|

| | | | | |
|---|--|-----------------------|-------------------|----------------------|
|  | UL Listed Approval ID: E238705 | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | - | - |

| | | | | |
|---|---|-----------------------|-------------------|----------------------|
|  | cUL Listed Approval ID: E238705 | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | - | - |

2305059

<https://www.phoenixcontact.com/us/products/2305059>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242220 |
| ECLASS-15.0 | 27242220 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000237 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

FLK 20/2FLK14/EZ-DR/ 50/KONFEK - Cable



2305059

<https://www.phoenixcontact.com/us/products/2305059>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com