

2202030

<https://www.phoenixcontact.com/us/products/2202030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Locking element for locking the PCB onto UM-BASIC/PRO housing at level 3



Your advantages

- Different base profiles, each with three PCB levels
- Module covers of different geometries can be positioned in any way
- Compatibility with many standard connection technologies
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2202030 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | AC13 |
| Product key | ACHDAZ |
| GTIN | 4055626005416 |
| Weight per piece (including packing) | 0.306 g |
| Weight per piece (excluding packing) | 0.3 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|----------------|------------------------------|
| Product type | Mounting material |
| Housing type | Press-drawn section housings |
| Housing type | Extruded profile housings |
| Housing series | UM-BASIC |
| Product family | UM-PRO |

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Glow-wire test

| | |
|------------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 125 °C |
| Test duration | 1 h |
| Force | 20 N |

Mechanical strength / tumbling barrel

| | |
|----------------|------------------------|
| Specification | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm |
| Frequency | 50 |

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

UM-BASIC/PRO PCB C-LOCK L3KMGY - Locking



2202030

<https://www.phoenixcontact.com/us/products/2202030>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202030>



UL Recognized

Approval ID: E240868

2202030

<https://www.phoenixcontact.com/us/products/2202030>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-BASIC/PRO PCB C-LOCK L3KMGY - Locking



2202030

<https://www.phoenixcontact.com/us/products/2202030>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com