

UK 5-HESI LEUCHTANZEIGE 24 - LED display



2202220

<https://www.phoenixcontact.com/us/products/2202220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LED display, color: transparent



Commercial data

Item number	2202220
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1234
GTIN	4017918269296
Weight per piece (including packing)	1.662 g
Weight per piece (excluding packing)	1.662 g
Customs tariff number	85318070
Country of origin	IN

2202220

<https://www.phoenixcontact.com/us/products/2202220>

Technical data

Product properties

Product type	LED display
--------------	-------------

Material specifications

Color	transparent
-------	-------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

UK 5-HESI LEUCHTANZEIGE 24 - LED display



2202220

<https://www.phoenixcontact.com/us/products/2202220>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202220>



EAC

Approval ID: KZ7500651131219505

UK 5-HESI LEUCHTANZEIGE 24 - LED display



2202220

<https://www.phoenixcontact.com/us/products/2202220>

Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 10.0	EC000899
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 5-HESI LEUCHTANZEIGE 24 - LED display



2202220

<https://www.phoenixcontact.com/us/products/2202220>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.054 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com