

# HS LC-H-D2/ R4XC10-2,54 - Fiber optic



2202323

<https://www.phoenixcontact.com/us/products/2202323>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiple light guides with glare protection, passive, rigid, Raised head, emission surface: spherical, number of displays: 40, (4 rows, 10 columns), pitch: 2.54 mm, ESD protection: <8 kV, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

## Your advantages

- Light guides are perfectly matched to electronics housings
- Easy mounting on the PCB using press pins
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2202323       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | AC05          |
| Product key                          | ACGABA        |
| GTIN                                 | 4055626050249 |
| Weight per piece (including packing) | 3.02 g        |
| Weight per piece (excluding packing) | 3.02 g        |
| Customs tariff number                | 90019000      |
| Country of origin                    | TN            |

## Technical data

### Notes

|               |  |
|---------------|--|
| Assembly note | Please observe the application note in the download area.                            |
| General       | To prevent glare, the system has an aperture. This also makes mixed colors possible. |

### Product properties

|                      |   |
|----------------------|---|
| Product type         | Fiber optic                                 |
| Number of positions  | 40  |
| Pitch                | 2.54 mm                                     |
| Number of rows       | 4   |
| Alignment            | Horizontal                                  |
| Conductor type       | Multiple light guides with glare protection |
| Head form            | Raised head                                 |
| Number of indicators | 40 (4 rows x 10 columns)                    |

### Electrical properties

|                |        |
|----------------|--------|
| ESD protection | < 8 kV |
|----------------|--------|

### Dimensions

|               |         |
|---------------|---------|
| Diameter      | 2 mm    |
| Hole diameter | 1.2 mm  |
| Pitch         | 2.54 mm |

### Material specifications

|  |                  |
|--|------------------|
| Color (Light guide)                    | transparent      |
| Color (Cover)                          | black (RAL 9005) |
| Material Light guide                   | Polycarbonate    |
| Material Cover                         | Polycarbonate    |
| Flammability rating according to UL 94 | HB               |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Max. IP code to attain          | IP20             |
| Ambient temperature (operation) | -40 °C ... 85 °C |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | Press-in |
|---------------|----------|

# HS LC-H-D2/ R4XC10-2,54 - Fiber optic



2202323

<https://www.phoenixcontact.com/us/products/2202323>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27460404 |
| ECLASS-13.0 | 27460404 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HS LC-H-D2/ R4XC10-2,54 - Fiber optic



2202323

<https://www.phoenixcontact.com/us/products/2202323>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)