

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, 8U, Marking lid, width: 18.8 mm, height: 110.95 mm, color: transparent



## Your advantages

- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2202627       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 5 pc          |
| Sales key                            | AC15          |
| Product key                          | ACHEBB        |
| GTIN                                 | 4055626210902 |
| Weight per piece (including packing) | 9.3 g         |
| Weight per piece (excluding packing) | 9.2 g         |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

## Technical data

### Product properties

|                              |                          |
|------------------------------|--------------------------|
| Product type                 | Upper housing part       |
| Housing type                 | DIN rail housing         |
| Housing type                 | Multifunctional housings |
| Housing series               | ME-IO                    |
| Product family               | ME-IO 18,8               |
| Ventilation openings present | no                       |

### Dimensions

|        |           |
|--------|-----------|
| Width  | 18.8 mm   |
| Height | 110.95 mm |

### Material specifications

|  |             |
|--|-------------|
| Color (Upper housing part)             | transparent |
| Material Upper housing part            | PA          |
| Flammability rating according to UL 94 | V0          |
| CTI according to IEC 60112             | 600         |

### Environmental and real-life conditions

#### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration           | 2g (58.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

#### Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-11:2014-02 |
| Temperature      | 850 °C                 |
| Time of exposure | 30 s                   |

#### Thermal stability / ball thrust test

|               |                        |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature   | 125 °C                 |
| Test duration | 1 h                    |
| Force         | 20 N                   |

#### Mechanical strength / tumbling barrel

|                |                        |
|----------------|------------------------|
| Specification  | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm                  |

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

|           |    |
|-----------|----|
| Frequency | 50 |
|-----------|----|

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Specification                  | IEC 60068-2-27:2008-02            |
| Pulse shape                    | Semi-sinusoidal                   |
| Acceleration                   | 15g                               |
| Shock duration                 | 11 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |

## Test for substances that would hinder coating with paint or varnish

|               |                    |
|---------------|--------------------|
| Specification | VDMA 24364:2018-05 |
|---------------|--------------------|

## Degree of protection (IP code)

|               |   |
|---------------|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---|

## Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

## Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

## Packaging specifications

|                      |        |
|----------------------|--------|
| Type of packaging    | PE bag |
| Outer packaging type | Carton |

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202627>



**UL Recognized**  
Approval ID: E240868

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ME-IO 18,8 MC 8U TRANS - Marking lid



2202627

<https://www.phoenixcontact.com/us/products/2202627>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)