

UM-RJ45/RJ11/MKDS - Termination board



2306197

<https://www.phoenixcontact.com/us/products/2306197>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and two RJ45 sockets, for mounting on NS 32 or NS 35/7.5

Commercial data

Item number	2306197
Packing unit	5 pc
Minimum order quantity	30 pc
Product key	DK2A83
GTIN	4017918961695
Weight per piece (including packing)	47.76 g
Weight per piece (excluding packing)	34.642 g
Country of origin	DE

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	< 50 V AC/DC
Max. current carrying capacity per branch	1 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μ s)

Connection data

RJ45 connection

Number of connections	2
Number of positions	8

COMBICON connection

Connection method	Screw connection
Number of positions	4
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 16

Dimensions

Item dimensions

Width	23 mm
Height	90 mm
Depth	52 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	max. 2000 m

Standards and regulations

UM-RJ45/RJ11/MKDS - Termination board



2306197

<https://www.phoenixcontact.com/us/products/2306197>

Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM-RJ45/RJ11/MKDS - Termination board



2306197

<https://www.phoenixcontact.com/us/products/2306197>

Classifications

UNSPSC

UNSPSC 21.0	39121432
-------------	----------

2306197

<https://www.phoenixcontact.com/us/products/2306197>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com