

UM 122-PROFIL PA L7,23CM KMGY - Profile



2203015

<https://www.phoenixcontact.com/us/products/2203015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Basic profile, profile width (internal): 122 mm, profile width (external): 127.5 mm, length: 72.3 mm



Commercial data

Item number	2203015
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHDBA
GTIN	4055626298139
Weight per piece (including packing)	38.7 g
Weight per piece (excluding packing)	35.9 g
Country of origin	DE

2203015

<https://www.phoenixcontact.com/us/products/2203015>

Technical data

Product properties

Product type	Lower housing part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM122
Ventilation openings present	no

Dimensions

Length	72.3 mm
--------	---------

External dimensions

Profile width (external)	127.5 mm
--------------------------	----------

Internal dimensions

Profile width (internal)	122 mm
--------------------------	--------

Material specifications

Color (Housing)	light gray (RAL 7035)
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

UM 122-PROFIL PA L7,23CM KMGY - Profile



2203015

<https://www.phoenixcontact.com/us/products/2203015>

Classifications

ECLASS

ECLASS-13.0

27190601

ETIM

ETIM 9.0

EC002779

UNSPSC

UNSPSC 21.0

31261500

UM 122-PROFIL PA L7,23CM KMGY - Profile



2203015

<https://www.phoenixcontact.com/us/products/2203015>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com