

MCR-PAC-T-USB - Programming adapter



2309000

<https://www.phoenixcontact.com/us/products/2309000>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Programming adapter with USB and T port interface, 2.4 m for programming FA MCR-..., MCR-...-LP-..., and MCR-...-HT-... modules



Commercial data

Item number	2309000
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C401
Product key	DK114Z
GTIN	4046356606233
Weight per piece (including packing)	128 g
Weight per piece (excluding packing)	124 g
Customs tariff number	84718000
Country of origin	DE

MCR-PAC-T-USB - Programming adapter



2309000

<https://www.phoenixcontact.com/us/products/2309000>

Technical data

Product properties

Product type	Programming adapter
--------------	---------------------

Dimensions

Width	56 mm
Height	24.5 mm
Depth	80 mm

Material specifications

Housing material	ABS
------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C

EMC data

Noise immunity	EN 61000-6-2
----------------	--------------

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

MCR-PAC-T-USB - Programming adapter



2309000

<https://www.phoenixcontact.com/us/products/2309000>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2309000>



EAC

Approval ID: RU C-DE.A*08.B.01837

MCR-PAC-T-USB - Programming adapter



2309000

<https://www.phoenixcontact.com/us/products/2309000>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

MCR-PAC-T-USB - Programming adapter



2309000

<https://www.phoenixcontact.com/us/products/2309000>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com