

PSI-MODEM-BASIC/USB - Modem



2313436

<https://www.phoenixcontact.com/us/products/2313436>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Industrial analog modem for assembly on EN DIN rails. For dialed operation in Europe, USA and Canada. Mini-USB type B interface, electrical 2-way isolation, supply voltage 5 V DC via the USB connection

Your advantages

- Callback function
- Configurable, selective call acceptance
- Integrated surge protection to ensure high system availability
- Connection establishment with password protection
- High-quality electrical isolation

Commercial data

Item number	2313436
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN24
Product key	DNC411
GTIN	4046356441391
Weight per piece (including packing)	248.9 g
Weight per piece (excluding packing)	92.6 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Modem
--------------	-------

Electrical properties

Electrical isolation	PSTN // USB
Maximum power dissipation for nominal condition	0.5 W
Mains type	Fixed-line network
Test voltage data interface/power supply	1.5 kV
Test voltage data interfaces	1500 V

Supply

Nominal supply voltage	5 V DC (Via mini USB type B)
Typical current consumption	< 100 mA (for 5 V DC, nominal operation)
	< 40 mA (for 5 V DC, sleep mode)

Connection data

Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

Interfaces

Data: USB 1.1

Connection method	Mini USB type B
Transmission length	5 m

Data: PSTN-Port (a/b-Line)

Connection method	RJ12, 6-pos.
Dialing procedure	Multiple frequency/pulse dialing, configuration via software

Dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA V0

2313436

<https://www.phoenixcontact.com/us/products/2313436>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C

Approvals

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 55032
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

PSI-MODEM-BASIC/USB - Modem

2313436

<https://www.phoenixcontact.com/us/products/2313436>



Classifications

UNSPSC

UNSPSC 21.0	43222628
-------------	----------

PSI-MODEM-BASIC/USB - Modem



2313436

<https://www.phoenixcontact.com/us/products/2313436>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com