PSM-SET-SCRJ-DUP/2-HCS/PN - FO connectors

2313546

https://www.phoenixcontact.com/us/products/2313546

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, SC-RJ, MM, 2-position, degree of protection: IP20, color: black



SC-RJ

Your advantages

- Suitable for quick and easy field assembly or repair
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Ideal for PCF graded-index (GI) fibers
- Compact design, thanks to SC-RJ pin connector pattern
- No bonding or polishing

Commercial data

Item number	2313546
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAB
GTIN	4046356480086
Weight per piece (including packing)	43 g
Weight per piece (excluding packing)	43 g
Customs tariff number	85367000
Country of origin	DE

Set consists of

VS-SCRJ-HCS-FA-IP20-PN - FO connectors

1404087

https://www.phoenixcontact.com/us/products/1404087



FO connectors, SC-RJ, Ethernet, MM, 2-position, connection method: mechanical splice, material: Plastic, degree of protection: IP20, color: black

Technical data

Product properties

Product type	Fiber optic connector (cable side)
Type	SC-RJ
Number of positions	2
Cable outlet	straight

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Dimensions

Width	16.5 mm
Height	11 mm
Length	88.5 mm

Material specifications

Color	black
Flammability rating according to UL 94	V0

Cable/line

Cable type	for all common PCF cable types
External cable diameter	2.2 mm ... 2.2 mm
Individual wire diameter	2.2 mm

FO cable

Number of fibers	2
Fiber type	PCF
Attenuation	≤ 1.5 dB
Transmission medium	FO

Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Classifications

ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

ETIM

ETIM 10.0	EC001122

UNSPSC

UNSPSC 21.0	43223300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com