

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB connector, 9-pos., pin, 90° cable outlet, bus system: PROFIBUS DP up to 12 Mbps with PG D-SUB socket for connecting a programming device, termination resistor can be switched on via slide switch, pin assignment: 3, 5, 6, 8; IDC terminal block connection

Product description

The D-SUB series, SUBCON-PLUS-PROFIB/... was specially designed for use in PROFIBUS systems up to 12 Mbps. Under field conditions, it allows convenient and fast connection of the incoming and outgoing bus cable. The terminating resistor is already integrated in all versions. It can be connected externally by means of a slide switch. At the same time, the outgoing bus segment is switched off. This makes it easy to start up segment by segment while incorrect terminations are avoided.

Your advantages

- Suitable for all common Fast Connect PROFIBUS cables and RS-485 bus lines



Commercial data

Item number	2313685
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN10
Product key	DNC531
GTIN	4046356514576
Weight per piece (including packing)	43.54 g
Weight per piece (excluding packing)	32.06 g
Customs tariff number	85366990
Country of origin	DE

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Data plug
MTTF	6706 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	1817 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	155 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
Pin assignment	3, 5, 6, 8

Electrical properties

Test voltage	50 V
Maximum power dissipation for nominal condition	0.025 W
Nominal voltage U_N	5 V
Nominal current I_N	100 mA

Connection data

Tightening torque	... 1.2 Nm
-------------------	------------

D-SUB connection

Connection method	D-SUB connector
-------------------	-----------------

IDC terminal blocks

Connection method	IDC fast connection
Conductor cross-section, rigid min.	0.32 mm ²
Conductor cross-section, rigid max.	1 mm ²
Conductor cross-section flexible min.	0.32 mm ²
Conductor cross-section flexible max.	1 mm ²
Single-wire/terminal point, rigid AWG min.	22
Single-wire/terminal point, rigid AWG max.	18
Min. AWG conductor cross-section, flexible	22
Max. AWG conductor cross-section, flexible	18

Programming connection

Connection method	D-SUB socket
-------------------	--------------

Interfaces

Bus system	PROFIBUS DP
Signal	PROFIBUS


SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Dimensions

Dimensional drawing	
Width	16.8 mm
Height	34.8 mm
Length	72 mm

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material (Housing)	ABS (metal-plated)

Cable/line

External cable diameter	7.6 mm ... 8.4 mm (Incoming bus line)
-------------------------	---------------------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 200
Fixing screws	4-40 UNC
Tightening torque	0.4 Nm

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 15g, 11 ms period, half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-20 °C ... 75 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Approvals

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Standards and regulations

Free from substances that could impair the application of coating

VDMA 24364:2018-05

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector




2313685

<https://www.phoenixcontact.com/us/products/2313685>

Drawings

Dimensional drawing




Dimensional drawing

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector

2313685

<https://www.phoenixcontact.com/us/products/2313685>

Schematic diagram




Stripping specifications

SUBCON-PLUS-PROFIB/90/PB/IDC - D-SUB bus connector

2313685

<https://www.phoenixcontact.com/us/products/2313685>

Schematic diagram



Connecting cables

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Circuit diagram



Functional diagram of the connector range
SUBCON-PLUS-PROFIB/...

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2313685>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



CSA
Approval ID: 2437602

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440322

ETIM

ETIM 10.0	EC001132
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SUBCON-PLUS-PROFIB/90/PG/IDC - D-SUB bus connector



2313685

<https://www.phoenixcontact.com/us/products/2313685>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6e693fba-aa8c-4817-8c85-6fd1fb0461a7

EF3.1 Climate Change

CO2e kg	0.858 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com