

# PSI-REP-CNET - Repeater



2313737

<https://www.phoenixcontact.com/us/products/2313737>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular repeater for electrical isolation and increasing the range for ControlNet, 5 Mbps data rate, 4-way isolation, DIN-rail mountable, 24 V DC power supply

## Your advantages

- Bit retiming for unrestricted cascading of devices
- Approved for use in zone 2
- Supply voltage and data signals routed through the DIN rail connectors
- All connections can be plugged in using BNC plugs or a COMBICON screw terminal block
- Can be combined with PSI-MOS FO converters in a modular way using DIN rail connectors
- High-quality electrical isolation between all interfaces (ControlNet (A) // ControlNet (B) // power supply // DIN rail connector)
- Redundant power supply possible by means of optional system power supply unit

## Commercial data

Item number	2313737
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC124
GTIN	4046356513821
Weight per piece (including packing)	245 g
Weight per piece (excluding packing)	245 g
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Interface converter
MTTF	1856 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	837 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	345 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
MTBF	1187 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	254 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

### Electrical properties

Electrical isolation	VCC // CNET // CNET
Maximum power dissipation for nominal condition	0.91 W
Test voltage data interface/power supply	1.5 kV <sub>rms</sub> (50 Hz, 1 min.)

#### Supply

Supply voltage range	18 V DC ... 30 V DC (via pluggable COMBICON screw terminal block)
Nominal supply voltage	24 V DC
Typical current consumption	38 mA (24 V DC)
Max. current consumption	65 mA
	≤ 2 A (For operation in a joining station, via the DIN rail connector)

#### Function

Status and diagnostic indicators	Port A (module status indicator), port B (module status indicator)
----------------------------------	--

### Output data

#### Switching

Output name	Relay output
Number of outputs	1
Contact switching type	N/O contact
Minimum switching voltage	18 V DC
Maximum switching voltage	30 V DC
Limiting continuous current	500 mA

# PSI-REP-CNET - Repeater

2313737

<https://www.phoenixcontact.com/us/products/2313737>

## Connection data

### Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

## Interfaces

Bit distortion, input	± 35 %
Bit distortion, output	< 6.25 %
Signal	ControlNet™


Data: ControlNet interface, in accordance with EN 50170

Serial transmission speed	5 Mbps
Connection method	BNC 75 Ω
Transmission length	≤ 1000 m
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section AWG max.	14
Conductor cross-section AWG min.	24
File format/coding	Serial asynchronous UART/NRZ

Data: ControlNet interface, in accordance with EN 50170

Serial transmission speed	5 Mbps
Connection method	BNC 75 Ω
Transmission length	≤ 1000 m
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section AWG max.	14
Conductor cross-section AWG min.	24
File format/coding	Serial asynchronous UART/NRZ

## Dimensions

Dimensional drawing	
Width	35 mm
Height	108 mm
Depth	117 mm

## Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA 6.6-FR

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g, 11 ms period, half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### ATEX

Identification	⊕ II 3 G Ex nA IIC T4 Gc X
Note	Please follow the special installation instructions in the documentation!

### UL, USA/Canada

Identification	508 Listed
----------------	------------

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2

### Noise emission

Standards/regulations	EN 55011
-----------------------	----------

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Contact discharge	± 6 kV
Discharge in air	± 8 kV
Comments	Criterion B

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

#### Electromagnetic HF field

Frequency range	80 MHz ... 3 GHz
Field intensity	10 V/m
Comments	Criterion A

#### Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

#### Fast transients (burst)

Input	± 2 kV
Signal	± 2 kV
Comments	Criterion B

#### Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

#### Surge current load (surge)

Input	± 0.5 kV
Signal	± 1 kV
Comments	Criterion B

#### Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

#### Conducted interference

Comments	Criterion A
Voltage	10 V

#### Emitted interference

Standards/regulations	EN 55011
Comments	Class A, industrial applications

#### Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

#### Standards and regulations

Free from substances that could impair the application of coating	in accordance with VW-AUDI-Seat central standard P-VW 3.10.7 57 65 0
---	--

#### Mounting

Mounting type	DIN rail mounting
---------------	-------------------


# PSI-REP-CNET - Repeater

2313737


<https://www.phoenixcontact.com/us/products/2313737>



## Drawings




Application drawing




Star structure

Application drawing



Tree structure


Application drawing



Branch line

Application drawing


## Linear structure



☒ = Switch on bus termination resistor

Line structure

Application drawing



Tap



Node



Terminator



Repeater


# PSI-REP-CNET - Repeater

2313737

<https://www.phoenixcontact.com/us/products/2313737>



Schematic diagram



Function elements


# PSI-REP-CNET - Repeater

2313737

<https://www.phoenixcontact.com/us/products/2313737>




Schematic diagram




Device connections

Diagram



Block diagram



## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)