

PSI-MODEM-BASIC/RS232/SET1 - Modem



2313753

<https://www.phoenixcontact.com/us/products/2313753>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Industrial analog modem for assembly on EN DIN rails. Worldwide access to industrial PCs, machines and systems. Serial RS-232 interface, 3-way electrical isolation, supply voltage 24 V DC.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2313753 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DN12 |
| Product key | DNC41C |
| GTIN | 4046356522434 |
| Weight per piece (including packing) | 202.7 g |
| Weight per piece (excluding packing) | 117.8 g |
| Customs tariff number | 85176200 |
| Country of origin | DE |

2313753

<https://www.phoenixcontact.com/us/products/2313753>

Technical data

Product properties

| | |
|--------------|-------|
| Product type | Modem |
|--------------|-------|

Electrical properties

| | |
|---|--------------------|
| Maximum power dissipation for nominal condition | 2.4 W |
| Mains type | Fixed-line network |

Interfaces

| | |
|--------|--------|
| Signal | RS-232 |
|--------|--------|

Dimensions

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 99 mm |
| Depth | 118.6 mm |

Approvals

Corrosive gas test

| | |
|----------------|----------------------------------|
| Identification | ISA-S71.04-1985 G3 Harsh Group A |
|----------------|----------------------------------|

PSI-MODEM-BASIC/RS232/SET1 - Modem



2313753

<https://www.phoenixcontact.com/us/products/2313753>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222628 |
|-------------|----------|

2313753

<https://www.phoenixcontact.com/us/products/2313753>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com