

2203191

<https://www.phoenixcontact.com/us/products/2203191>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Display housing, 15", light gray, central window, front level, with cutout for connection technology angle plate consisting of two half shells with screws

Your advantages

- Display housing for portable and stationary operating panels
- Integration of TFT display and membrane keypads
- Up to IP54 degree of protection
- Shock-resistant ABS plastic
- Flammability rating V0 in accordance with UL 94

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2203191 |
| Packing unit | 4 pc |
| Minimum order quantity | 4 pc |
| Sales key | AC02 |
| Product key | ACFBAA |
| GTIN | 4055626378459 |
| Weight per piece (including packing) | 756 g |
| Weight per piece (excluding packing) | 756 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

2203191

<https://www.phoenixcontact.com/us/products/2203191>

Technical data


Product properties

| | |
|------------------------------|------------------|
| Product type | Complete housing |
| Housing type | Display carrier |
| Housing type | Display carriers |
| Housing series | DCS |
| Product family | DCS 15.. |
| Ventilation openings present | no |
| Battery compartment | no |

Display

| | |
|----------|---------------------------------------|
| Diagonal | 15 in. / 38.3 cm (Window for display) |
|----------|---------------------------------------|

Dimensions

| | |
|----------------------|--|
| Dimensional drawing |  |
| Width | 363 mm |
| Height | 286 mm |
| Depth | 62 mm |
| Dimensions | 306 mm x 230 mm (Window for display, center position) 24.5 mm x 213 mm (Front with faceplate, position below, quantity 1, angled plate) |
| Front with faceplate | lower angled plate, 2 x (213 mm x 24.5 mm) |

PCB design

| | |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material Housing | ABS |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 400 ≤ CTI < 600 |
| Insulating material | II |
| Surface characteristics | untreated |

Environmental and real-life conditions

Glow-wire test

| | |
|---------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |

DCS 15 M C O S C 7035 - Electronics housing



2203191

<https://www.phoenixcontact.com/us/products/2203191>

| | |
|------------------|------|
| Time of exposure | 30 s |
|------------------|------|

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 80 °C |
| Test duration | 1 h |
| Force | 20 |

Degree of protection (IP code)

| | |
|---------------|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---|

Ambient conditions

| | |
|------------------------|------|
| Max. IP code to attain | IP54 |
|------------------------|------|

PCB data

| | |
|-----------------------|-------------------|
| Number of PCB holders | 2 |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

Mounting

| | |
|-------------------|-----|
| Wall fastening | no |
| Mounting position | any |

2203191

<https://www.phoenixcontact.com/us/products/2203191>

Drawings



Schematic representation – for additional information, see product range drawing in the Download Center

2203191

<https://www.phoenixcontact.com/us/products/2203191>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190103 |
| ECLASS-15.0 | 27190103 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001031 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

2203191

<https://www.phoenixcontact.com/us/products/2203191>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com