KP HC-ALU 100 K4 C4 P6 - Membrane keypad

2203574

https://www.phoenixcontact.com/us/products/2203574

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Membrane keypad, self-adhesive, copper conduction technology, 4 keys, embossed, 4 colors, connecting cable: 47.3 mm, pitch: 1.0 mm, operating temperature: 0 °C ... 45 °C

Commercial data

Item number	2203574
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFAAD
GTIN	4055626485270
Weight per piece (including packing)	15.2 g
Weight per piece (excluding packing)	15.2 g
Customs tariff number	85371098
Country of origin	HU

Technical data

Product properties

Product type	Membrane keypad
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU
Technology	Conductive silver technology
Number of positions	4
Pitch	1 mm
Embossing	Dome embossing 11 x 11 mm
Number of socket pins	6
Number of keys	4

Dimensions

Length	47.3 mm (Membrane cable)
Pitch	1 mm
Dimensions	95 mm x 72 mm

Material specifications

Material	Polyester

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 45 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

Mounting

Mounting type	Self-adhesive

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com