

# KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Membrane keypad, self-adhesive, copper conduction technology, 4 keys, embossed, 4 colors, connecting cable: 47.3 mm, pitch: 1.0 mm, operating temperature: 0 °C ... 45 °C



## Commercial data

Item number	2203574
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFAAD
GTIN	4055626485270
Weight per piece (including packing)	15.2 g
Weight per piece (excluding packing)	15.2 g
Customs tariff number	85371098
Country of origin	HU

# KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

## Technical data

### Product properties

Product type	Membrane keypad
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU
Technology	Conductive silver technology
Number of positions	4
Pitch	1 mm
Embossing	Dome embossing 11 x 11 mm
Number of socket pins	6
Number of keys	4

### Dimensions

Length	47.3 mm (Membrane cable)
Pitch	1 mm
Dimensions	95 mm x 72 mm

### Material specifications

Material	Polyester
----------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 45 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

### Mounting

Mounting type	Self-adhesive
---------------	---------------

# KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# KP HC-ALU 100 K4 C4 P6 - Membrane keypad



2203574

<https://www.phoenixcontact.com/us/products/2203574>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)