

# HCS-C MEDIUM D-SEAL 2,8 - Seal




2203737

<https://www.phoenixcontact.com/us/products/2203737>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing frame, self-adhesive, lasered, for 2.8" display



## Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2203737       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC02          |
| Product key                          | ACFACZ        |
| GTIN                                 | 4055626485430 |
| Weight per piece (including packing) | 3.2 g         |
| Weight per piece (excluding packing) | 3.2 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# HCS-C MEDIUM D-SEAL 2,8 - Seal



2203737

<https://www.phoenixcontact.com/us/products/2203737>

## Technical data

### Product properties

|                              |                  |
|------------------------------|------------------|
| Product type                 | Seal             |
| Housing type                 | Handheld housing |
| Housing series               | HCS              |
| Product family               | HCS              |
| Ventilation openings present | no               |

### Dimensions

|        |         |
|--------|---------|
| Width  | 75 mm   |
| Height | 45.2 mm |
| Depth  | 2 mm    |

### Environmental and real-life conditions

#### Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-11:2014-02 |
| Temperature      | 850 °C                 |
| Time of exposure | 30 s                   |

#### Thermal stability / ball thrust test

|               |                        |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature   | 80 °C                  |
| Test duration | 1 h                    |
| Force         | 20                     |

# HCS-C MEDIUM D-SEAL 2,8 - Seal



2203737

<https://www.phoenixcontact.com/us/products/2203737>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HCS-C MEDIUM D-SEAL 2,8 - Seal



2203737

<https://www.phoenixcontact.com/us/products/2203737>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)