
HCS-T MINI DISPLAY PLATE - Fixing plate

2203864

https://www.phoenixcontact.com/us/products/2203864

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Display plate for securing the display



Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

Commercial data

Item number	2203864
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFABZ
GTIN	4055626489049
Weight per piece (including packing)	17.91 g
Weight per piece (excluding packing)	17.81 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	Mounting material
Housing type	Handheld housing
Housing series	HCS
Ventilation openings present	no

Dimensions

Width	77 mm
Height	79.5 mm
Depth	2 mm

Material specifications

Color (Housing)	transparent
Material	PC

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	80 °C
Test duration	1 h
Force	20

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com