

FB-2SP/E - Device coupler

2316052

<https://www.phoenixcontact.com/us/products/2316052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device coupler for Foundation Fieldbus and PROFIBUS PA with terminal connections for two spurs connected to fieldbus end devices

Product description

The FB-2SP/E has terminal blocks for two spur connections to each device coupler. The device coupler provides short-circuit protection to the fieldbus trunk. Voltage and communication are routed via the TBUS connection system to multiple installed device couplers.

Commercial data

Item number	2316052
Packing unit	1 pc
Sales key	DN11
Product key	DNC144
GTIN	4055626000916
Weight per piece (including packing)	109.4 g
Weight per piece (excluding packing)	109.4 g
Customs tariff number	85389099
Country of origin	US

Technical data

Notes

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Product properties

Product type	Device coupler
--------------	----------------

Electrical properties

Supply

Supply voltage range	10.5 V DC ... 32 V DC (via FB-ET/E)
Max. current consumption	3.5 mA (No-load)

Connection data

Supply

Conductor cross-section, flexible	2.50 mm ² ... 0.20 mm ²
Conductor cross-section, rigid	2.50 mm ² ... 0.20 mm ²
Conductor cross-section, flexible [AWG]	24 ... 12
Conductor cross-section AWG	24 ... 12

Ex data

Safety data

Inductance L_i	0 μ H
Capacitance C_i	0 nF
Max. output voltage U_o	U_i
Max. output current I_o	50 mA (per spur)
Max. output power P_o	$U_o \times I_o$
IIC: Max. external inductivity L_o / Max. external capacitance C_o	/ 60 nF 250 μ H

Interfaces

Signal	PROFIBUS
	FOUNDATION Fieldbus

Data: Foundation Fieldbus and PROFIBUS PA Segment

Connection method	Pluggable COMBICON screw connection for each spur
No. of channels	2
Tightening torque	0.5 Nm ... 0.6 Nm
Termination resistor	via FB-ET/E
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section flexible min.	0.2 mm ²

FB-2SP/E - Device coupler



2316052

<https://www.phoenixcontact.com/us/products/2316052>

Conductor cross-section, rigid max.	2.5 mm ²
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24
Output nominal voltage	≤ 32 V (per spur)
Maximum output current	45 mA (per spur)

Dimensions

Width	17.5 mm
Height	89.7 mm
Depth	70.4 mm

Material specifications

Color	green
Housing material	PA 6.6-FR

Mechanical tests

Corrosive resistance in accordance with ANSI-ISA 71.04-1985 - Severity level G3	:
---	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (depending on set rated current)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	< 95 % (non-condensing)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	15g, 11 ms
Vibration (operation)	10 Hz ... 150 Hz, 1g

Approvals

Conformity/Approvals

Fieldbus Foundation	FF-846
EN	EN 61326, EN 60068-2-27, EN 60068-2-6, EN 60079-0, EN 60079-11, EN 60079-15
NE	NAMUR NE 21

Ex data

ATEX	Sira 14ATEX4018X; Ⓢ II 3(3)G Ex nA [ic] IIC T4 Gc; Ex nA [ic] IIC T4 Gc, FISCO ic spurs
IECEX	IECEX SIR 14.0011X; Ex nA [ic] IIC T4 Gc; Ex nA [ic] IIC T4 Gc, FISCO ic spurs

CSA, USA/Canada	<p>Class I, Div. 2, Groups A,B,C,D Ex nL IIC T4 FNICO, Ex ic IIC T4 FISCO ic Ex nA [nL] IIC T4, Ex nA [ic] IIC T4 Ex nA [nL] IIC T4 FNICO spurs, Ex nA [ic] IIC T4 FISCO ic spurs Class I, Zone 2 AEx nL IIC T4 FNICO, AEx ic IIC T4 FISCO ic AEx nA [nL] IIC T4, AEx nA [ic] IIC T4 AEx nA [nL] IIC T4 FNICO spurs, AEx nA [ic] IIC T4 FISCO ic spurs</p>
-----------------	---

Standards and regulations

Standards

Standards/regulations	IEC 60529, IEC 61158-2
	NE21
	EN 61326, EN 60068-2-27, EN 60068-2-6, EN 60079-0, EN 60079-11, EN 60079-15
	FF-846

Standards/regulations

Standards/regulations	Ring wave noise immunity in acc. with IEC 61000-4-12
-----------------------	--

Standards/regulations

Standards/regulations	Dry heat in acc. with IEC 61131-2
-----------------------	-----------------------------------

Standards/regulations

Standards/regulations	Damp heat in acc. with IEC 61131-2
-----------------------	------------------------------------

Standards/regulations

Standards/regulations	Shock and vibration in acc. with EN 61131-2 and EN 50178
Standards/regulations	IEC 61158-2

Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715

FB-2SP/E - Device coupler


2316052

<https://www.phoenixcontact.com/us/products/2316052>



Drawings

Circuit diagram



Connection diagram: FB-2SP

FB-2SP/E - Device coupler

2316052

<https://www.phoenixcontact.com/us/products/2316052>



Classifications

ETIM

ETIM 9.0	EC001600
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FB-2SP/E - Device coupler



2316052

<https://www.phoenixcontact.com/us/products/2316052>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	724f47d3-7afe-4999-b8ff-fb5a9ec1cbc1

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com