

# FB-PS-PLUG-24DC/28DC/0.5/EX - Power module



2316132

<https://www.phoenixcontact.com/us/products/2316132>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power supply plug for fieldbus system in hazardous locations. Provides 500 mA @ 28 V DC to couplers along the trunk.

## Commercial data

Item number	2316132
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC1Z1
GTIN	4046356619981
Weight per piece (including packing)	250 g
Weight per piece (excluding packing)	218 g
Customs tariff number	85044083
Country of origin	US

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Input data

Input voltage	24 V DC
Nominal input voltage range	18.5 V DC ... 30.5 V DC
Input voltage range DC	18.5 V DC ... 30.5 V DC
Short-term input voltage	24 V DC

### Output data

Output voltage range	28 V DC ... 30 V DC (on the trunk)
Nominal output current ( $I_N$ )	500 mA
Output power	13.5 W
Power dissipation	4 W (typical)
Connection in parallel	yes, for redundancy
Connection in series	no

### Connection data


#### Output

Connection method	Plug-in connection
-------------------	--------------------

### Product properties

Product type	Power supply
--------------	--------------

### Dimensions

Dimensional drawing	
Width	17.5 mm
Height	117.6 mm
Depth	115 mm

### Mounting

Assembly note	Plug-in connections may only be operated only when there is no load/voltage.
---------------	--

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)

## Standards and regulations

### Standards

Standards/regulations	NE21
	EN 61326
Standards/specifications	Ring wave noise immunity in acc. with IEC 61000-4-12
Standards/specifications	Dry heat in acc. with IEC 61131-2
Standards/specifications	Damp heat in acc. with IEC 61131-2
Standards/specifications	Shock and vibration in acc. with EN 61131-2 and EN 50178
Standards/specifications	IEC 61158-2

## Approvals

### Conformity/Approvals

Fieldbus Foundation	FF-831
EN	EN 61326
NE	NAMUR NE 21

### Ex data

ATEX	Sira 11ATEX4216X; II 3 G Ex nA nC IIC T4 Gc
IECEX	IECEX SIR 11.0097X; Ex nA nC IIC T4 Gc
CSA, USA/Canada	Class I, Div. 2, Groups A, B, C, D; Ex nA nC IIC T4 Class I, Zone 2, AEx nA nC IIC T4

## Ex data

### Safety data

Input voltage $U_i$	30.5 V DC (input power)
Input current $I_i$	850 mA (input power)
Inductance $L_i$	17.6 mH (trunk and host)
Max. output voltage $U_o$	30 V DC (trunk and host)

# FB-PS-PLUG-24DC/28DC/0.5/EX - Power module




2316132

<https://www.phoenixcontact.com/us/products/2316132>


## Drawings

Dimensional drawing



Power supply base and plug

Block diagram



Connection diagram: FB-PS-PLUG-24DC/28DC/0.5/EX

2316132

<https://www.phoenixcontact.com/us/products/2316132>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2316132>



**EAC**

Approval ID: RU C-DE.A\*30.B.01082



**IECEX**

Approval ID: IECEX SIR 11.0097X



**CSA**

Approval ID: 2431654



**CSAus**

Approval ID: 2431654



**ATEX**

Approval ID: Sira 11ATEX4216X



**CCC**

Approval ID: 2022122303115621

# FB-PS-PLUG-24DC/28DC/0.5/EX - Power module



2316132

<https://www.phoenixcontact.com/us/products/2316132>

## Classifications

### ECLASS

ECLASS-13.0

27242611

### ETIM

ETIM 9.0

EC002583

### UNSPSC

UNSPSC 21.0

32151600

2316132

<https://www.phoenixcontact.com/us/products/2316132>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ce0d6386-8850-4746-8134-f007870932ad

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)