

# FB-DIAG/FF/LI - Device coupler



2316284

<https://www.phoenixcontact.com/us/products/2316284>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Field diagnostics module, legacy installation, includes pluggable side connector



## Commercial data

Item number	2316284
Packing unit	1 pc
Sales key	DN11
Product key	DNC1Z1
GTIN	4046356783248
Weight per piece (including packing)	114.3 g
Weight per piece (excluding packing)	114.3 g
Customs tariff number	85389099
Country of origin	US

## Technical data

### Notes

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Product properties

Product type	Device coupler
--------------	----------------

### Electrical properties

#### Supply

Supply voltage range	9 V DC ... 32 V DC
Typical current consumption	27 mA
Max. current consumption	29 mA

### Ex data

#### Safety data

Input voltage $U_i$	32 V DC
Input current $I_i$	274 mA (IIC)
	570 mA (IIB)
Inductance $L_i$	10 $\mu$ H
Capacitance $C_i$	0 $\mu$ F


### Interfaces

Signal	PROFIBUS
	FOUNDATION Fieldbus

#### Data: FOUNDATION Fieldbus

Connection method	Pluggable screw connection with test points
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24

### Dimensions

Dimensional drawing	
---------------------	--

Width	17.7 mm
Height	93.9 mm
Depth	70.4 mm

## Material specifications

Color	green
Flammability rating according to UL 94	V0

## Mechanical tests

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms half-sine shock pulse
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 5g, 10 ... 150 Hz
Corrosive resistance in accordance with ANSI-ISA 71.04-1985 - Severity level G3	:

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)

## Approvals

### Conformity/Approvals

Conformance	IEC 61158-2
Fieldbus Foundation	FF-830
EN	EN 61326, EN 60068-2-27, EN 60068-2-6
NE	NE21

### Ex data

ATEX	Sira 13ATEX4149X; Ⓢ II 3G Ex nA [ic] IIC T4 Gc
IECEX	IECEX SIR 13.0060X; Ex nA [ic] IIC T4 Gc
CSA, USA/Canada	Class I, Div. 2, Groups A,B,C,D; Ex nA nL IIC T4 Gc Class I, Zone 2, AEx nA nC IIC T4 Gc

## Standards and regulations

### Standards/regulations

Standards/regulations	Ring wave noise immunity in acc. with IEC 61000-4-12
-----------------------	--

### Standards/regulations

Standards/regulations	Dry heat in acc. with IEC 61131-2
-----------------------	-----------------------------------

### Standards/regulations

Standards/regulations	Damp heat in acc. with IEC 61131-2
-----------------------	------------------------------------

### Standards/regulations

# FB-DIAG/FF/LI - Device coupler



2316284

<https://www.phoenixcontact.com/us/products/2316284>

Standards/regulations	Shock and vibration in acc. with EN 61131-2 and EN 50178
Standards/regulations	IEC 61158-2

## Mounting

Mounting type	DIN rail mounting
Mounting position	Any orientation on DIN rail, NS 35, in acc. with EN 60715


# FB-DIAG/FF/LI - Device coupler

2316284


<https://www.phoenixcontact.com/us/products/2316284>

## Drawings

Dimensional drawing



Block diagram



# FB-DIAG/FF/LI - Device coupler



2316284

<https://www.phoenixcontact.com/us/products/2316284>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2316284>



**IECEx**

Approval ID: IECEx SIR 13.0060X



**ATEX**

Approval ID: Sira 13ATEX4149X

# FB-DIAG/FF/LI - Device coupler



2316284

<https://www.phoenixcontact.com/us/products/2316284>

## Classifications

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2316284

<https://www.phoenixcontact.com/us/products/2316284>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)