

# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 200 A AC primary current; 5 A AC secondary current; accuracy class 1; 5 VA rated power

## Commercial data

Item number	2276120
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA11
GTIN	4046356502757
Weight per piece (including packing)	520.4 g
Weight per piece (excluding packing)	445.3 g
Customs tariff number	85043129
Country of origin	DE

# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

## Technical data

### Product properties

Product type	Current transformer
Product family	Window-type current transformer

### Electrical properties

Rated insulation voltage	1 kV (Phase/neutral conductor)
--------------------------	--------------------------------

### General

Can be calibrated	no
Converter type	Window-type current transformer

### Input data

#### Current transformer

Rated power	5 VA
Thermal rated short-time current	$I_{th} = 60 * I_n$
Thermal rated continuous current	$I_d = 1.2 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency $f_n$	50 Hz 60 Hz
Primary rated current $I_{pn}$	0 A AC ... 200 A AC
Can be calibrated	no
Converter type	Window-type current transformer

### Output data

#### Signal

Designation	Current output
Secondary rated current $I_{sn}$	5 A AC
Surge current limitation factor	FS 5
Accuracy class	1

### Connection data

Connection method	Screw connection
Conductor cross-section flexible	2x 2.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Secondary terminals with screw connection)

### Dimensions

#### Item dimensions

Width	30 mm
Height	108 mm
Depth	85 mm

#### Item dimensions with alternative mounting

# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Width	85 mm
Height	108 mm
Depth	30 mm

## Copper rail

Width	50 mm
Height	12 mm

## Copper rail 2

Width	40 mm
Height	10 mm

## Circular conductor

Diameter	42 mm
----------	-------

## Material specifications

Color	black (RAL 9005)
Housing material	PA 6.6

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C
Altitude	≤ 1000 m
Permissible humidity (operation)	Use only indoors, non-condensing
Insulating material class	E

## Approvals

### UL, USA/Canada

Identification	XODW8.E323953
----------------	---------------

## Standards and regulations

Standards/regulations	EN 61869
-----------------------	----------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer




2276120

<https://www.phoenixcontact.com/us/products/2276120>

## Drawings

Dimensional drawing



# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

## Classifications

### ECLASS

ECLASS-13.0

27210902

### ETIM

ETIM 9.0

EC002048

### UNSPSC

UNSPSC 21.0

39121000

# PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)