PACT-FAST-MNT-W13-L65 - Mounting material

2276625

https://www.phoenixcontact.com/us/products/2276625

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Quick-action transformer mounting for black PACT current transformers (not compatible with gray PACT current transformers), positioning pins: 65 mm, retaining tab: 13 mm

Commercial data

Item number	2276625
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA1Z
GTIN	4046356658348
Weight per piece (including packing)	61.55 g
Weight per piece (excluding packing)	55.2 g
Customs tariff number	39269097
Country of origin	CN

Technical data

Notes

Order information:	The 16 mm wide converter attachment can also be used for larger current transformers if the length of the fixing pins is sufficient.


Product properties

Product type	Mounting material

Connection data

Tightening torque	0.4 Nm

Dimensions

Dimensional drawing	
Width	13 mm
Depth	65 mm


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C

Drawings

Dimensional drawing



Classifications

ECLASS

ECLASS-13.0	27210992

ETIM

ETIM 9.0	EC002498

UNSPSC

UNSPSC 21.0	39121000

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com