

# UM-2KS50/ 8DO/RS/Z/SO225 - Output module




2319032

<https://www.phoenixcontact.com/us/products/2319032>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

16-channel digital output module with spring-cage connection and redundant voltage supply.  
Suitable for Yokogawa SDV 531/-L card.



## Commercial data

Item number	2319032
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2A8N
GTIN	4046356340649
Weight per piece (including packing)	619.2 g
Weight per piece (excluding packing)	603.7 g
Country of origin	DE

# UM-2KS50/ 8DO/RS/Z/SO225 - Output module



2319032

<https://www.phoenixcontact.com/us/products/2319032>

## Technical data

### Product properties

Product type	Interface module
--------------	------------------

#### Insulation characteristics: Air clearances and creepage distances

Overvoltage category	III
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	30 V DC
Max. current carrying capacity per branch	600 mA
Max. total current of all branches	6.3 A

#### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.8 kV (Basic insulation)

#### Supported controller: YOKOGAWA ProSafe-RS

Suitable I/O card	SDV531L
-------------------	---------

### Connection data

#### Field level

Connection method	Spring-cage connection
Number of positions	16
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Tightening torque	0.5 Nm

#### Supply

Connection method	Spring-cage connection
Number of positions	6
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Signaling

Status display present	yes
------------------------	-----

### Dimensions

# UM-2KS50/ 8DO/RS/Z/SO225 - Output module



2319032

<https://www.phoenixcontact.com/us/products/2319032>

## Item dimensions

Width	152.5 mm
Height	126 mm
Depth	97 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
---------------------------------	------------------

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# UM-2KS50/ 8DO/RS/Z/SO225 - Output module



2319032

<https://www.phoenixcontact.com/us/products/2319032>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)