

UM-FLK14/8RM/MSTB/ 683-DO - Relay module



2319744

<https://www.phoenixcontact.com/us/products/2319744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE relay module, with COMBICON screw connection and one 14-pos. flat-ribbon cable connector, 1 changeover contact, plug-in base for 8 miniature relays, input voltage 24 V DC

Commercial data

Item number	2319744
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2A88
GTIN	4046356427722
Weight per piece (including packing)	293.5 g
Weight per piece (excluding packing)	280.2 g
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Product properties

Product type	Relay Module
--------------	--------------

Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2

Insulation characteristics: Air and creepage distances, output/output

Insulation	Functional insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Air clearances and creepage distances, input/output

Rated insulation voltage	260 V
Rated surge voltage	6 kV (1.2/50 μ s)

Air and creepage distances, output/output

Rated insulation voltage	260 V
Rated surge voltage	4 kV (1.2/50 μ s)

Input data

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	0.8 ... 1.2
Input voltage range	19.2 V DC ... 28.8 V DC
Typical input current at U_N	Related to the assembly
Protective circuit	Damping diode, polarity protection diode
Status display/channel	Yellow LED

Output data

Switching

Contact switching type	1 changeover contact
Maximum switching voltage	250 V AC/DC
Limiting continuous current	3 A

UM-FLK14/8RM/MSTB/ 683-DO - Relay module



2319744

<https://www.phoenixcontact.com/us/products/2319744>

Connection data

Supply

Connection method	Screw connection
Number of positions	2
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Field level

Connection method	Screw connection
Number of positions	9
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection in acc. with standard	IEC 60603-13
Connection method	Flat-ribbon cable connection
Number of connections	1
Number of positions	14

Dimensions

Width	111 mm
Height	126 mm
Depth	64 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

2319744

<https://www.phoenixcontact.com/us/products/2319744>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com