

UM-FLK14/PTS/MSTB/3723-DI - Input module



2319757

<https://www.phoenixcontact.com/us/products/2319757>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital VARIOFACE input module, with COMBICON screw connection and a 14-pos. flat-ribbon cable connector. The signal path can be interrupted with a knife disconnection.

Commercial data

Item number	2319757
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2A81
GTIN	4046356427753
Weight per piece (including packing)	234.4 g
Weight per piece (excluding packing)	210.3 g
Country of origin	DE

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	50 V DC (25 V AC)
Max. current carrying capacity per branch	1 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μ s)

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw/plug-in connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	14
Pitch	2.54 mm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	64 mm
Height	126 mm
Depth	66 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

UM-FLK14/PTS/MSTB/3723-DI - Input module



2319757

<https://www.phoenixcontact.com/us/products/2319757>

Housing insulation material	PVC
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM-FLK14/PTS/MSTB/3723-DI - Input module



2319757

<https://www.phoenixcontact.com/us/products/2319757>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2319757

<https://www.phoenixcontact.com/us/products/2319757>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com