

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cast front adapter with attached round cable and a 40-pos. socket strip injection-molded on both sides for the connection of Yokogawa controllers. Cable length: 19.0 m

Your advantages

- Molded connectors
- Lateral cable outlet of the I/O module
- Can be screwed on
- KS/AKB-compatible connectors on the module side

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2321622 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK222N |
| GTIN | 4046356340274 |
| Weight per piece (including packing) | 2.996 kg |
| Weight per piece (excluding packing) | 2.996 kg |
| Customs tariff number | 85444290 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Front adapter |
|--------------|---------------|

Electrical properties

| | |
|------------------------|-----------------------|
| Operating voltage (DC) | ≤ 30 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path) | ≤ 500 mA (uncoiled) |

Supported controller: YOKOGAWA CS3000 CentumVP

| | |
|-------------------|--------|
| Suitable I/O card | AAI543 |
| | AAI141 |
| | AAI143 |
| | AAI835 |
| | AAI841 |
| | AAI135 |
| | AAR181 |
| | AAT141 |
| | AAV141 |
| | AAV142 |
| | AAB841 |
| | AAV542 |

Supported controller: YOKOGAWA STARDOM

| | |
|-------------------|---------|
| Suitable I/O card | NFAI543 |
| | NFAI141 |
| | NFAI143 |
| | NFAI835 |
| | NFAI841 |
| | NFAI135 |
| | NFAV141 |
| | NFAV142 |
| | NFAB841 |
| | NFAV542 |

Supported controller: YOKOGAWA ProSafe-RS

| | |
|-------------------|--------|
| Suitable I/O card | SAI143 |
| | SAV144 |
| | SAI533 |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
|----------------------------------|------------------------------|

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

| | |
|-----------------------------|--------------------------------|
| Connection method | Yokogawa, I/O cards compatible |
| Number of connections | 1 |
| Number of positions | 40 |
| Tightening torque | 0.5 Nm (Screw connection) |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | Yokogawa, KS compatible |
| Number of connections | 1 |
| Number of positions | 40 |
| Tightening torque | 0.5 Nm (Screw connection) |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Dimensions

Cable

| | |
|--------|------|
| Length | 19 m |
|--------|------|

Cable/line

40X0.14 [PVC]

| | |
|---|---|
| UL AWM Style | 2464/1061 |
| Number of positions | 40 |
| Shielded | yes |
| Cable type | 40X0.14 [PVC] |
| Conductor type | Assembled shielded round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 40x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 9.80 mm ±0.3 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 101 mm |
| Smallest bending radius, movable installation | 182 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter) |
| Halogen-free | no |
| Flame resistance | IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) |

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

| | |
|-------------------|---|
| | IEC 60332-3-22 (raw cable) |
| | UL VW-1 |
| | CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP20 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Approvals

UKCA

| | |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

Drawings

Connection diagram

| 40-pos. connector the I/O card | 40-pos. connector to the module | Wire color |
|--------------------------------------|---------------------------------------|---------------|
| 1 | 40 | black |
| 2 | 39 | brown |
| 3 | 38 | red |
| 4 | 37 | orange |
| 5 | 36 | yellow |
| 6 | 35 | green |
| 7 | 34 | blue |
| 8 | 33 | violet |
| 9 | 32 | gray |
| 10 | 31 | white |
| 11 | 30 | white-black |
| 12 | 29 | white-brown |
| 13 | 28 | white-red |
| 14 | 27 | white-orange |
| 15 | 26 | white-yellow |
| 16 | 25 | white-green |
| 17 | 24 | white-blue |
| 18 | 23 | white-violet |
| 19 | 22 | white-gray |
| 20 | 21 | brown-black |
| 21 | 20 | brown-red |
| 22 | 19 | brown-orange |
| 23 | 18 | brown-yellow |
| 24 | 17 | brown-green |
| 25 | 16 | brown-blue |
| 26 | 15 | brown-violet |
| 27 | 14 | brown-gray |
| 28 | 13 | brown-white |
| 29 | 12 | green-black |
| 30 | 11 | green-brown |
| 31 | 10 | green-red |
| 32 | 9 | green-orange |
| 33 | 8 | green-blue |
| 34 | 7 | green-violet |
| 35 | 6 | green-gray |
| 36 | 5 | green-white |
| 37 | 4 | yellow-black |
| 38 | 3 | yellow-brown |
| 39 | 2 | yellow-red |
| 40 | 1 | yellow-orange |

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

Classifications

ECLASS

ECLASS-13.0

27242292

ETIM

ETIM 9.0

EC002584

UNSPSC

UNSPSC 21.0

32151600

FLK 40-PA/EZ-DR/KS/1900/YUC - Front adapter



2321622

<https://www.phoenixcontact.com/us/products/2321622>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com