

VIP-2/SC/HD15SUB/M - Termination board



2322326

<https://www.phoenixcontact.com/us/products/2322326>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with screw connection and high density D-Subminiature male connector, for mounting on NS 35 rails, no. of pos.: 15, width: 57 mm



Your advantages

- Screw connection
- 1:1 connection

Commercial data

Item number	2322326
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2112
GTIN	4046356451253
Weight per piece (including packing)	87.1 g
Weight per piece (excluding packing)	100.3 g
Customs tariff number	85366990
Country of origin	US

2322326

<https://www.phoenixcontact.com/us/products/2322326>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	15

Electrical properties

Operating voltage (AC)	25 V AC
Operating voltage (DC)	60 V DC
Current (per branch)	≤ 1 A

Connection data

Connection 1 (control level)

Connection method	High density D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	15

Connection 2 (field level)

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	16
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	44.9 mm
Height	65.5 mm
Depth	45.1 mm

Material specifications

Color	gray (RAL 7042)
Housing insulation material	Polyamide PA non-reinforced

2322326

<https://www.phoenixcontact.com/us/products/2322326>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-2/SC/HD15SUB/M - Termination board




2322326


<https://www.phoenixcontact.com/us/products/2322326>

Drawings

Dimensional drawing



Circuit diagram



Universal circuit diagram

VIP-2/SC/HD15SUB/M - Termination board





2322326

<https://www.phoenixcontact.com/us/products/2322326>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2322326>

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

VIP-2/SC/HD15SUB/M - Termination board



2322326

<https://www.phoenixcontact.com/us/products/2322326>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2322326

<https://www.phoenixcontact.com/us/products/2322326>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c1801bae-8729-4b24-8d79-58aa34c03364

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com