

WP 06T/WT - Web panel



2400163

<https://www.phoenixcontact.com/us/products/2400163>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Web panel, 14.5 cm / 5.7"-TFT display (Analog resistive (GFG), anti-reflective coating), 320 x 240 pixel(s) (QVGA), 65536 colors, Arm9™, 184 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, MicroBrowser, without bus system.

Your advantages

- UV resistance
- Extended temperature range of -20 °C ... +70 °C
- High degree of protection: IP67 (front)
- High resistance to abrasion for the front
- High chemical resistance (glass touch)
- Easy device replacement - the visualization project is saved on the PLC
- Display can be read in sunlight
- Energy efficient due to LED backlighting
- Neutral front
- Easy installation, low installation depth, and compact design
- Short startup time

Commercial data

Item number	2400163
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRCACD
GTIN	4046356965927
Weight per piece (including packing)	700 g
Weight per piece (excluding packing)	700 g
Customs tariff number	84714100
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
Application	Rugged

Computer data

Processor	Arm9™, 184 MHz
Operating system	Windows® CE 5.0
RAM	128 MB SDRAM
Data storage system	Flash, 64 MB

Display

Display type	14.5 cm / 5.7"-TFT
Readability in sunlight	yes
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	Analog resistive (GFG), anti-reflective coating
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	40000 h
Color spectrum	65536 colors

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	MicroBrowser
---------------	--------------

Electrical properties

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.2 A

Supply

Power consumption	typ. 4.8 W
-------------------	------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
	5 % ... 95 % (front; non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
	5 % ... 95 % (front; non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Dimensions

Width	195 mm
Height	153 mm
Depth	47 mm

External dimensions

Width / Height / Depth	195 mm / 153 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	161 mm / 119 mm / 42 mm (Installation cutout)
-------------------------------------	---

WP 06T/WT - Web panel

2400163

<https://www.phoenixcontact.com/us/products/2400163>



Classifications

UNSPSC

UNSPSC 21.0	43211904
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------