
# FLKM 50/S7/A-S400 - Passive module

2294432

https://www.phoenixcontact.com/us/products/2294432

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows version FLKM 50/S5/A-S 115

VARIOFACE interface module, for I/Os of the SIMATIC® S7-400, with SIMATIC®-specific marking, only in conjunction with FLKM 50-PA-S400

## Commercial data

| | |
|---|---|
| Item number | 2294432 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK218S |
| GTIN | 4017918154844 |
| Weight per piece (including packing) | 243 g |
| Weight per piece (excluding packing) | 174.32 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Interface module |
| Product family | VARIOFACE |
| Number of positions | 50 |
| No. of channels | 16 |
| Operating mode | 100% operating factor |

Insulation characteristics: Air clearances and creepage distances

| | |
|---|---|
| Insulation | Functional insulation |
| Overvoltage category | II |
| Pollution degree | 2 |

## Electrical properties

| | |
|---|---|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Current (per branch) | ≤ 1 A |
| Current (Voltage supply per byte) | ≤ 2 A |

Air clearances and creepage distances

| | |
|---|---|
| Rated insulation voltage | 63 V |
| Rated surge voltage | 0.6 kV (1.2/50 µs) |

Supported controller: SIEMENS S7-400

| | |
|---|---|
| Suitable I/O card | 6ES7421-1BL01-0AA0 |
| | 6ES7421-7BH01-0AB0 |
| | 6ES7421-7DH00-0AA0 |
| | 6ES7422-1BL00-0AA0 |
| | 6ES7422-7BL00-0AB0 |

## Connection data

Connection 1 (control level)

| | |
|---|---|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2 (field level)

| | |
|---|---|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Number of positions | 40 |

| | |
|---|---|
| Conductor cross-section rigid | 0.2 mm² ... 4 mm² |
| Conductor cross-section rigid (2 conductors with same cross section) | 0.2 mm² ... 1.5 mm² |
| Conductor cross-section flexible | 0.2 mm² ... 2.5 mm² |
| | 0.25 mm² ... 1.5 mm² (Ferrule without plastic sleeve) |
| | 0.25 mm² ... 2.5 mm² (Ferrule with plastic sleeve) |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.2 mm² ... 1.5 mm² |
| | 0.25 mm² ... 0.75 mm² (Ferrule without plastic sleeve) |
| | 0.5 mm² ... 0.5 mm² (TWIN ferrule with plastic sleeve) |
| Conductor cross-section AWG | 24 ... 12 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |
| Pitch | 5.08 mm |

## Signaling

| | |
|---|---|
| Status display present | no |

## Dimensions

Item dimensions

| | |
|---|---|
| Width | 113 mm |
| Height | 90 mm |
| Depth | 68 mm |

## Material specifications

| | |
|---|---|
| Color | green (RAL 6021) |
| Housing insulation material | PVC |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection (Module) | IP00 |
| Degree of protection (Installation location) | ≥ IP54 |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Altitude | ≤ 2000 m |

## Approvals

UKCA

| | |
|---|---|
| Certificate | UKCA-compliant |

## Standards and regulations

Air clearances and creepage distances

| | |
|---|---|
| Standards/regulations | EN IEC 60664-1 |

## Mounting


| | |
|---|---|
| Mounting type | DIN rail mounting |
| Mounting position | any |

## Notes

| | |
|---|---|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |

## Drawings

Circuit diagram




Connection scheme: FLKM 50/S7/A-S400

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2294432

**cUL Recognized**
Approval ID: E238705

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 2 A | - | - |

**UL Recognized**
Approval ID: E238705

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 2 A | - | - |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002780 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com