

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 12 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2296223 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK2211 |
| GTIN | 4017918462123 |
| Weight per piece (including packing) | 1,858.3 g |
| Weight per piece (excluding packing) | 1,858 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|----------------------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating) |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

Supported controller: SIEMENS S7-1500

| | |
|-------------------|--------------------|
| Suitable I/O card | 6ES7521-1BL00-0AB0 |
| | 6ES7521-1BL10-0AA0 |
| | 6ES7522-1BL00-0AB0 |
| | 6ES7522-1BL01-0AB0 |
| | 6ES7522-1BL10-0AA0 |
| | 6ES7523-1BL00-0AA0 |
| | 6ES7531-7KF00-0AB0 |
| | 6ES7531-7LH00-0AB0 |
| | 6ES7531-7MH00-0AB0 |
| | 6ES7531-7NF00-0AB0 |
| | 6ES7531-7NF10-0AB0 |
| | 6ES7531-7PF00-0AB0 |
| | 6ES7532-5HF00-0AB0 |

Supported controller: SIEMENS S7-300 / ET 200 M

| | |
|-------------------|--------------------|
| Suitable I/O card | CPU 313C |
| | CPU 313C-2DP |
| | CPU 313C-2PtP |
| | CPU 314C-2DP |
| | CPU 314C-2PtP |
| | 6ES7321-1BL00-0AA0 |
| | 6ES7322-1BL00-0AA0 |

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

| | |
|--|--------------------|
| | 6ES7322-8BH01-0AB0 |
| | 6ES7323-1BL00-0AA0 |
| | 6ES7331-1KF01-0AB0 |
| | 6ES7331-7NF00-0AB0 |
| | 6ES7331-7NF10-0AB0 |
| | 6ES7331-7PF01-0AB0 |
| | 6ES7331-7PF11-0AB0 |
| | 6ES7332-5HF00-0AB0 |
| | 6ES7350-2AH01-0AE0 |
| | 6ES7357-4AH01-0AE0 |

Supported controller: SIEMENS S7-400

| | |
|-------------------|--------------------|
| Suitable I/O card | 6ES7421-1BL01-0AA0 |
| | 6ES7421-7BH01-0AB0 |
| | 6ES7421-7DH00-0AA0 |
| | 6ES7422-1BL00-0AA0 |
| | 6ES7422-7BL00-0AB0 |
| | 6ES7431-0HH0-0AB0 |
| | 6ES7431-1KF00-0AB0 |
| | 6ES7431-1KF10-0AB0 |
| | 6ES7431-1KF20-0AB0 |
| | 6ES7431-7KF00-0AB0 |
| | 6ES7431-7KF10-0AB0 |
| | 6ES7431-7QH00-0AB0 |
| | 6ES7432-1HF00-0AB0 |

Supported controller: SCHNEIDER ELECTRIC Modicon TSX QUANTUM

| | |
|-------------------|---------|
| Suitable I/O card | DDI 353 |
| | DDI 841 |
| | DDI 853 |
| | DAI 340 |
| | DAI 440 |
| | DAI 453 |
| | DDO 353 |
| | DDM 390 |
| | ACI 030 |
| | ACI 040 |
| | ATI 030 |
| | ARI 030 |
| | AVI 030 |
| | ACO 020 |
| | ACO 130 |
| | AVO 020 |
| | EHC 105 |
| | EHC 202 |

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

Supported controller: ALLEN-BRADLEY ControlLogix

| | |
|-------------------|------------|
| Suitable I/O card | 1756-IA16I |
| | 1756-IB16D |
| | 1756-IB16I |
| | 1756-IB32 |
| | 1756-IH16I |
| | 1756-OB32 |
| | 1756-IF8 |
| | 1756-IF16 |
| | 1756-HSC |
| | 1756-M02AE |

Supported controller: HONEYWELL Experion PKS C200

| | |
|-------------------|------------|
| Suitable I/O card | TC-IDK 161 |
| | TC-IDX 161 |
| | TC-IDJ 161 |
| | TC-IDD 321 |
| | TC-ODD 321 |
| | TC-IAH 161 |

Cable/line

| | |
|--------------|------|
| Cable length | 12 m |
|--------------|------|

50X0.14 [PVC]

| | |
|---|---|
| UL AWM Style | 2464/1061 |
| Number of positions | 50 |
| Shielded | no |
| Cable type | 50X0.14 [PVC] |
| Conductor type | Round cable set |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 50x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 10.30 mm ±0.4 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 86 mm |
| Smallest bending radius, movable installation | 161 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |
| Halogen-free | no |
| | IEC 60332-1-2 (raw cable) |

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

| | |
|-------------------|---|
| Flame resistance | VDE 0842, Part 332-1-2 (raw cable) |
| | IEC 60332-3-22 (raw cable) |
| | UL VW-1 |
| | CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Cable for one module |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Diagram



Maximum permissible current per path in uncoiled state

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

Classifications

ECLASS

ECLASS-13.0

27242220

ETIM

ETIM 9.0

EC000237

UNSPSC

UNSPSC 21.0

26121600

FLK 50/EZ-DR/1200/KONFEK - Cable



2296223

<https://www.phoenixcontact.com/us/products/2296223>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com