

# TPE121ZGS/800930026 S00078 - Panel PC



2401258

<https://www.phoenixcontact.com/us/products/2401258>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Panel PC, 30.7 cm / 12.1"-TFT display (Analog resistive (GFG)), 800 x 600 pixel(s) (SVGA), 262144 colors, Intel® Atom™ E680T 1.6 GHz, 4x USB Host 2.0, 1x COM (RS-232), 1x COM (RS-232/485), 1 x Ethernet (10/100/1000 Mbps), RJ45, Windows® Embedded Standard 7, TSvisiT, DualCAN.

Similar figure

## Commercial data

Item number	2401258
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRBACK
GTIN	4055626107820
Weight per piece (including packing)	2,750 g
Weight per piece (excluding packing)	2,750 g
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---------------------------------------------------------------------------

### Product properties

Product type	Panel PC
Application	Rugged

#### Computer data

Processor	Intel® Atom™ E680T 1.6 GHz
Operating system	Windows® Embedded Standard 7
RAM	2 GB DDR2 SDRAM
Data storage system	SATA DOM SSD (SLC), 32 GB
Slots	1x SD

#### Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	Analog resistive (GFG)
Display lighting type	LED
Brightness	360 cd/m <sup>2</sup> typical (adjustable)
MTBF	50000 h
Color spectrum	262144 colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	65.00 °
Reading angle bottom	75.00 °

### System properties

User software	TSvisIT
---------------	---------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

#### Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

#### Real-time clock

Realtime clock	Yes
----------------	-----

### Interfaces

	4x USB Host 2.0
--	-----------------

2401258

<https://www.phoenixcontact.com/us/products/2401258>

Interfaces	1x COM (RS-232)
	1x COM (RS-232/485)
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	DualCAN

## Dimensions

### External dimensions

Width / Height / Depth	359 mm / 280 mm / 5 mm (Dimensions of the front plate)
------------------------	--------------------------------------------------------

### Installation dimensions

Width / Height / Installation depth	323 mm / 244 mm / 110 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	------------------------------------------------------------------------------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Altitude	4000 m
Permissible humidity (operation)	5 % ... 95 % (Front)
	20 % ... 85 % (On the rear)
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

2401258

<https://www.phoenixcontact.com/us/products/2401258>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)