TPM21AS/022360 S00001 - Touch panel

2401375

https://www.phoenixcontact.com/us/products/2401375

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Similar figure

Maritime-Touch panel; 14.5 cm / 5.7"-TFT display (analog resistive (polyester)); 320 x 240 pixel(s) (QVGA); 256 colors; Processor: Arm9™, 200 MHz; Interfaces: 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45; Operating system: Windows® CE 5.0; Software: TSvisRT; without bus system

Commercial data

Item number	2401375
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCBBB
GTIN	4055626146324
Country of origin	Information on the country of origin is provided with the delivery.

Technical data

Product properties

Product type	Operator panel
Application	Maritime

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB
Extras	Maritime without keys

Display

Display type	14.5 cm / 5.7"-TFT
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	40000 h
Color spectrum	256 colors
Reading angle left	75.00 °
Reading angle right	75.00 °
Reading angle top	60.00 °
Reading angle bottom	75.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	TSvisRT

Electrical properties

Service life of battery	5 years (typical)

Supply

Typical current consumption	0.5 A

Real-time clock

Real-time clock	Yes

Supply

Power supply unit	24 V DC ±20 %

Mounting

Mounting type	Front mounting

Material specifications

Material front plate	Aluminum (black anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	0.7g, in accordance with EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	203 mm / 165 mm / 5 mm (Dimensions of the front plate)

Installation dimensions

Width / Height / Installation depth	157 mm / 195 mm / 56 mm

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com