

HT06AT/732050/311/00100 S00001 - Mobile panel



2401380

<https://www.phoenixcontact.com/us/products/2401380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile panel, 8.9 cm / 3.5"-TFT display (analog resistive (polyester)), 65536 colors, Arm9™, 200 MHz, 1x USB Host 2.0, without, Windows® CE 5.0, TSvisRT, MPI.

Similar figure

Commercial data

Item number	2401380
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCAEB
GTIN	4055626148687
Weight per piece (including packing)	2,500 g
Weight per piece (excluding packing)	2,500 g
Customs tariff number	84713000
Country of origin	DE

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	8.9 cm / 3.5"-TFT
Screen resolution	240 x 320 Pixel(s)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	320 cd/m ² typical (adjustable)
MTBF	30000 h
Color spectrum	65536 colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	80.00 °
Reading angle bottom	60.00 °

Interfaces

Interfaces	1x USB Host 2.0
Optional interfaces	none
Network	without
Bus system	MPI

System properties

User software	TSvisRT
---------------	---------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.25 A
-----------------------------	--------

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Mounting

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Mounting type	none
---------------	------

Material specifications

Material front plate	Plastic
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	145 mm / 265 mm / 67 mm
------------------------	-------------------------

HT06AT/732050/311/00100 S00001 - Mobile panel



2401380

<https://www.phoenixcontact.com/us/products/2401380>

Classifications

UNSPSC

UNSPSC 21.0	43211712
-------------	----------

2401380

<https://www.phoenixcontact.com/us/products/2401380>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com