

# UMK- 8 RM/REL-MR 24/1/SO93 - Multiple relay module



2300957

<https://www.phoenixcontact.com/us/products/2300957>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, 8-channel relay module, 2 changeover contacts, contact material (AgNi 90/10), input voltage 24 V DC

## Commercial data

Item number	2300957
Packing unit	1 pc
Minimum order quantity	20 pc
Product key	DK616Y
GTIN	4017918905804
Weight per piece (including packing)	340 g
Weight per piece (excluding packing)	340 g
Country of origin	DE

# UMK- 8 RM/REL-MR 24/1/SO93 - Multiple relay module



2300957

<https://www.phoenixcontact.com/us/products/2300957>

## Technical data

### Product properties

Product type	Relay Module
--------------	--------------

Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2

Insulation characteristics: Air and creepage distances, output/output

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

### Electrical properties

Air clearances and creepage distances, input/output

Rated insulation voltage	260 V
Rated surge voltage	6 kV (1.2/50 µs)

Air and creepage distances, output/output

Rated insulation voltage	260 V
Rated surge voltage	4 kV (1.2/50 µs)

### Input data

Nominal input voltage $U_N$	24 V DC
Input voltage range in reference to $U_N$	0.9 ... 1.1
Input voltage range	21.6 V DC ... 26.4 V DC
Typical input current at $U_N$	19 mA
Protective circuit	Freewheeling diode; Freewheeling diode
Status display/channel	Red LED

### Output data

Switching

Contact switching type	Single contact, 2 N/O contact
Contact material	AgNi (90/10) gold-plated
Maximum switching voltage	250 V AC/DC
Limiting continuous current	5 A

### Connection data

Controller level

Connection method	Screw connection
Number of positions	10
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

# UMK- 8 RM/REL-MR 24/1/SO93 - Multiple relay module



2300957

<https://www.phoenixcontact.com/us/products/2300957>

Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Field level

Connection method	Screw connection
Number of positions	5
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

Width	124 mm
Height	77 mm
Depth	70 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

### Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# UMK- 8 RM/REL-MR 24/1/SO93 - Multiple relay module



2300957

<https://www.phoenixcontact.com/us/products/2300957>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)