

# TP070SKW/200114041 S00127 - Touch panel



2401553

<https://www.phoenixcontact.com/us/products/2401553>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 17.8 cm / 7"-TFT display (projective-capacitive (PCAP)), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Arm® Cortex®-A8, 1000 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, IniNet Browser, without bus system.

## Commercial data

Item number	2401553
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCADD
GTIN	4055626247489
Weight per piece (including packing)	1,100 g
Weight per piece (excluding packing)	1,100 g
Country of origin	DE

## Technical data

### Product properties

Product type	Operator panel
--------------	----------------

### Computer data

Processor	Arm® Cortex®-A8, 1000 MHz
Operating system	Windows® Embedded Compact 7
RAM	512 MB LPDDR SDRAM 1 MB SRAM
Data storage system	NAND-Flash, 1 GB
Slots	1x SD
Extras	Integrated acoustic signal (buzzer)

### Display

Display type	17.8 cm / 7"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	400 cd/m <sup>2</sup> , typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	60.00 °
Reading angle bottom	60.00 °

### Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

### System properties

User software	IniNet Browser
---------------	----------------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

### Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.4 A

### Real-time clock

Realtime clock	Yes
----------------	-----

### Mounting

# TP070SKW/200114041 S00127 - Touch panel



2401553

<https://www.phoenixcontact.com/us/products/2401553>

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 45 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	5 % ... 95 % (front; non-condensing) 20 % ... 85 % (On the rear)
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	208 mm / 149 mm / 6 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	201 mm / 141 mm / 53 mm
-------------------------------------	-------------------------

# TP070SKW/200114041 S00127 - Touch panel



2401553

<https://www.phoenixcontact.com/us/products/2401553>

## Classifications

### UNSPSC

UNSPSC 21.0	43211904
-------------	----------

2401553

<https://www.phoenixcontact.com/us/products/2401553>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)