

TPE043SGB/200610021 S00071 - Touch panel



2401606

<https://www.phoenixcontact.com/us/products/2401606>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel, 10.92 cm / 4.3"-TFT display (Analog resistive (GFG)), 480 x 272 pixel(s) (WQVGA), 262144 colors, Arm® Cortex®-A8, 1000 MHz, 2x USB Host 2.0, 1x COM (RS-232), 1x COM (RS-422/485), 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, TSvisiT, DualCAN.

Similar figure

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2401606 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | DRCACE |
| GTIN | 4055626283555 |
| Weight per piece (including packing) | 600 g |
| Weight per piece (excluding packing) | 600 g |
| Country of origin | DE |

2401606

<https://www.phoenixcontact.com/us/products/2401606>

Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
| Application | Rugged |

Computer data

| | |
|---------------------|---------------------------------|
| Processor | Arm® Cortex®-A8, 1000 MHz |
| Operating system | Windows® Embedded Compact 7 |
| RAM | 1 MB SRAM 512 MB LPDDR SDRAM |
| Data storage system | NAND-Flash, 1 GB |
| Slots | 1x SD |

Display

| | |
|-----------------------|--------------------------------|
| Display type | 10.92 cm / 4.3"-TFT |
| Screen resolution | 480 x 272 Pixel(s) (WQVGA) |
| Touch technology | Analog resistive (GFG) |
| Display lighting type | LED |
| Brightness | 385 cd/m² typical (adjustable) |
| MTBF | 40000 h |
| Color spectrum | 262144 colors |
| Reading angle left | 75.00 ° |
| Reading angle right | 75.00 ° |
| Reading angle top | 63.00 ° |
| Reading angle bottom | 75.00 ° |

Interfaces

| | |
|---------------------|---|
| Interfaces | 2x USB Host 2.0 1x COM (RS-232) 1x COM (RS-422/485) |
| Optional interfaces | none |
| Network | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system | DualCAN |

System properties

| | |
|---------------|---------|
| User software | TSvisIT |
|---------------|---------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

Supply

| | |
|-----------------------------|---------------|
| Power supply unit | 24 V DC ±20 % |
| Typical current consumption | 0.2 A |

TPE043SGB/200610021 S00071 - Touch panel



2401606

<https://www.phoenixcontact.com/us/products/2401606>

Real-time clock

| | |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

Mounting

| | |
|---------------|-------------|
| Mounting type | Bolt fixing |
|---------------|-------------|

Material specifications

| | |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material | Steel sheet, zinc-plated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--------------------------------------|
| Degree of protection | IP67 (front), IP20 (back) NEMA 4X |
| Ambient temperature (operation) | -20 °C ... 70 °C |
| Ambient temperature (storage/transport) | -30 °C ... 80 °C |
| Permissible humidity (operation) | 20 % ... 85 % |
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 1g, according to EN 60068-2-6 |

Dimensions

External dimensions

| | |
|------------------------|--|
| Width / Height / Depth | 171 mm / 131 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

Installation dimensions

| | |
|-------------------------------------|--|
| Width / Height / Installation depth | 136 mm / 96 mm / 68 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|--|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com