

# TPM121XIT-12/3203C3600 S00006 - Touch panel



2401625

<https://www.phoenixcontact.com/us/products/2401625>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Similar figure

Maritime-Touch panel, 30.7 cm / 12.1"-TFT display (Resistive industrial touch screen), 800 x 600 pixel(s) (SVGA), 262144 colors, Xscale® PXA320, 806 MHz, 2x USB host 1.1, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, TSvisRT, without bus system.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2401625       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DRCBBB        |
| GTIN                                 | 4055626295206 |
| Weight per piece (including packing) | 2.5 kg        |
| Weight per piece (excluding packing) | 2.5 kg        |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Operator panel |
| Application  | Maritime       |

### Computer data

|                     |                           |
|---------------------|---------------------------|
| Processor           | Xscale® PXA320, 806 MHz   |
| Operating system    | Windows® CE 5.0           |
| RAM                 | 128 MB SDRAM<br>1 MB SRAM |
| Data storage system | NAND-Flash, 1 GB          |
| Extras              | Maritime with keys        |

### Display

|                       |  |
|-----------------------|--|
| Display type          | 30.7 cm / 12.1"-TFT                        |
| Screen resolution     | 800 x 600 Pixel(s) (SVGA)                  |
| Touch technology      | Resistive industrial touch screen          |
| Display lighting type | LED  |
| Brightness            | 360 cd/m <sup>2</sup> typical (adjustable) |
| MTBF                  | 50000 h                                    |
| Color spectrum        | 262144 colors                              |
| Reading angle left    | 80.00 °                                    |
| Reading angle right   | 80.00 °                                    |
| Reading angle top     | 60.00 °                                    |
| Reading angle bottom  | 80.00 °                                    |

### Interfaces

|                     |                                  |
|---------------------|----------------------------------|
| Interfaces          | 2x USB host 1.1                  |
| Optional interfaces | CF slot                          |
| Network             | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system          | without bus system               |

### System properties

|               |         |
|---------------|---------|
| User software | TSvisRT |
|---------------|---------|

### Electrical properties

|                         |                   |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

### Supply

|                             |               |
|-----------------------------|---------------|
| Power supply unit           | 24 V DC ±20 % |
| Typical current consumption | 0.7 A         |

### Real-time clock

|                |     |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

# TPM121XIT-12/3203C3600 S00006 - Touch panel



2401625

<https://www.phoenixcontact.com/us/products/2401625>

## Mounting

|               |                |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

## Material specifications

|                      |                           |
|----------------------|---------------------------|
| Material front plate | Aluminum (black anodized) |
| Housing material     | Steel sheet, zinc-plated  |

## Environmental and real-life conditions

### Ambient conditions

|   |                                       |
|---|---------------------------------------|
| Degree of protection                    | IP65 (front), IP20 (back)<br>NEMA 4X  |
| Ambient temperature (operation)         | 0 °C ... 55 °C                        |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C                      |
| Altitude                                | 3000 m                                |
| Permissible humidity (operation)        | 20 % ... 85 % (non-condensing)        |
| Shock                                   | 15g, according to IEC 60068-2-27      |
| Vibration (operation)                   | 0.7g, in accordance with EN 60068-2-6 |

## Dimensions

### External dimensions

|                        |  |
|------------------------|--|
| Width / Height / Depth | 340 mm / 285 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

### Installation dimensions

|                                     |   |
|-------------------------------------|---|
| Width / Height / Installation depth | 315 mm / 259 mm / 62 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|---|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)