VISU+ 2 EXPRESS - Visualization software

2402774

https://www.phoenixcontact.com/us/products/2402774

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Development environment for all touch panels with integrated runtime of the Visu+ visualization software.

Your advantages

- No license fees
- Maximum flexibility, thanks to the wide range of driver interfaces for leading controller manufacturers
- Time and cost savings, thanks to the simplified user interface
- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- HMI visualization
- Web access via the Visu+ mobile app
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL

Commercial data

Item number	2402774
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	00
Product key	DRDAAA
GTIN	4055626131856
Weight per piece (including packing)	68.9 g
Weight per piece (excluding packing)	68.9 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Product properties

Product type	Visualization

System properties

Intended use for the software	Visualization

License information

Type of license	Freeware

Functionality

Basic functions	Know-How protection and safety through encoding of projects
	FDA CFR 21 Part 11 compatible
	OPC Classic Interface and direct drivers
Expanded functionality	Web client capability
	Extended alarm management with SMS and e-mail function
Integrated function	Online configuration
	Password protection
	Language selection
	Alarm management
	Web client
	OPC server
Number of I/O nodes	0

System requirements

Processor	Intel® Celeron® / Pentium® 1.6 Hz
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Main memory (RAM)	min. 512 Mbyte (recommended: 1 GByte)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Screen resolution	1024 x 768 pixel(s) (XGA)

System requirements for development environment

Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012

	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003

System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
	Windows® Mobile

Classifications

ECLASS

ECLASS-13.0	27242502
ECLASS-15.0	27242502

ETIM

ETIM 10.0	EC001416

UNSPSC

UNSPSC 21.0	43231500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com