

# BL FPM 15.6 - Monitor



2402980

<https://www.phoenixcontact.com/us/products/2402980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP65-rated, 15.6-inch, flat -panel LCD monitor with projective capacitive touch screen

## Product description

The Basicline BL FPM 15.6 is an industrial flat-panel monitor that can be used in applications where a remote display location is required.

## Your advantages

- 15.6" display
- DisplayPort 1.2, VGA, and DVI-I input ports
- Integrated configuration buttons
- Ambient operating temperatures from -10 °C ... 60 °C
- 15.6" touch screen display

## Commercial data

Item number	2402980
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABD
GTIN	4055626202297
Weight per piece (including packing)	7,775 g
Weight per piece (excluding packing)	7,775 g
Customs tariff number	85299020
Country of origin	TW

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Monitor
--------------	---------

#### Computer data

Processor	without processor
Operating system	without operating system
RAM	without RAM
Data storage system	without data storage
Cooling	passive
Slots	without slots
Optical drive	without drive
Extras	without

#### Display

Display type	39.6 cm / 15.6"-TFT
Screen resolution	1366 x 768 Pixel(s) (WXGA)
Touch technology	projective-capacitive, ten-touch control
Display lighting type	LED
Brightness	300 cd/m <sup>2</sup> , typical (adjustable)
MTBF	> 50000 h
Color spectrum	16.7 million colors

### Electrical properties

#### Supply

Supply voltage	24 V DC (±10 %)
Power supply unit	24 V DC
Max. current consumption	0.59 A

### Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

### Interfaces

Interfaces	1x USB Type A (For touch control only) 1x DisplayPort
------------	--

# BL FPM 15.6 - Monitor



2402980

<https://www.phoenixcontact.com/us/products/2402980>

Monitor output	1x DVI-D
	1x VGA
Network	without network

## Dimensions

### External dimensions

Width / Height / Depth	417 mm / 312 mm / 51 mm
------------------------	-------------------------

### Installation dimensions

Width / Height / Installation depth	401 mm / 296 mm /
-------------------------------------	-------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Shock	15g, 11 ms impulse
Vibration (operation)	1g

## Mounting

Mounting type	Front mounting
	VESA holder
Holder system	VESA MIS-D 100 C

# BL FPM 15.6 - Monitor



2402980

<https://www.phoenixcontact.com/us/products/2402980>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2402980>



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00389

# BL FPM 15.6 - Monitor



2402980

<https://www.phoenixcontact.com/us/products/2402980>

## Classifications

### ECLASS

ECLASS-13.0

19200201

### ETIM

ETIM 9.0

EC001428

### UNSPSC

UNSPSC 21.0

43211900

2402980

<https://www.phoenixcontact.com/us/products/2402980>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f3e1e80b-0a54-41ee-8d46-1f242ee33dbd

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)