AXC F 2152 - Controller

2404267

https://www.phoenixcontact.com/us/products/2404267

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



Controller (SPS), PLCnext Control; Programming: High-level language and IEC 61131-3; Operating system: Yocto/Linux® (real-time); Programming tool: PLCnext Engineer, Eclipse®, Visual Studio®, MATLAB®/ Simulink®; Processor: Arm® Cortex®-A9, 2x 800 MHz; IoT connection: PROFICLOUD and every cloud via cloud connectors; Development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2 (Certification conditions see user documentation); The product is being prepared for compliance with the Cyber Resilience Act (CRA).

Product description

The PLCnext AXC F 2152 controller for the Axioline I/O system is fast, robust and easy to use. It has been consistently designed for maximum performance, easy handling and use in harsh industrial environments.

Your advantages

- Real-time-capable Linux operating system for deterministic and reliable execution of time-critical processes
- Supports numerous protocols such as: HTTP, HTTPS, FTP, OPC UA, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc. – for smooth communication with IT systems
- Direct connection to the Proficloud, the PLCnext Store and any cloud platforms – for seamless IoT integration of your applications
- Support for numerous fieldbus protocols (PROFINET, Modbus TCP/RTU, Ethernet/IP, etc.) for easy integration into existing automation technology systems and installations
- Maximum design freedom thanks to the combination of classic PLC programming with modern high-level languages such as C++, C#, or Python
- Meets the highest security requirements of industrial automation – for the protection of your applications and data

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	2404267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR09
Product key	DRADAC
GTIN	4055626356280
Weight per piece (including packing)	289 g
Weight per piece (excluding packing)	223 g
Customs tariff number	85371091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Controller
Product family	PLCnext Control
Type	modular
Special properties	Development process certified in accordance with IEC 62443-4-1
	Product certified in accordance with IEC 62443-4-2 Certification conditions see user documentation
	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
Overvoltage category	II
Pollution degree	2

Display

Diagnostics display	no

System properties

Operating system	Yocto/Linux® (real-time)
Processor	Arm®Cortex®-A9, 2x 800 MHz
Trusted Platform Module	TPM 1.2
Flash memory	512 Mbyte (internal flash memory)
RAM	512 Mbyte DDR3 SDRAM

IoT capability: PROFICLOUDIoT capability: PROFICLOUD

Supports cloud computing	yes
IoT platform	PROFICLOUD

IoT capability: Any-Cloud ConnectorIoT capability: Any-Cloud Connector

Supports cloud computing	yes
IoT platform	every cloud via cloud connectors

IEC 61131 runtime system

Program memory	8 Mbyte
Retentive data storage	48 kByte (NVRAM)
Data storage system	12 Mbyte

Cycle Time	1 ms (for cyclical task)
Number of data blocks	depending on data storage
Number of control tasks	32 (16 per processor core)

System limits Controller

Amount of process data (Axioline input/output data)	max. 1482 Byte (Total per station)
Amount of process data (Axioline input data)	max. 1024 Byte
Amount of process data (Axioline output data)	max. 1024 Byte
Number of supported devices (Axioline)	max. 63 (per station)
Number of IO-Link masters (Recommended/No test)	max. 8 (recommended)
Number of local bus devices that can be connected (Axioline)	max. 63 (observe current consumption)

PROFINET

Device function	PROFINET controller, PROFINET device
Conformance Class	B
Supported functions (PROFINET-Controller)	MRP FSU
Supported functions (PROFINET-Device)	MRP
Update rate	min. 1 ms (4 devices)
	min. 16 ms (64 devices)
Update rate min/max (Supports (device))	2 ms ... 250 ms
Process data width (PROFINET-Device)	64 Byte ... 512 Byte
Number of supported devices (PROFINET-Controller)	max. 64 (at PROFINET controller)
Number of slots	1
Device ID	0142_{hex}
Vendor ID	$00B0_{hex}$

Function

Diagnostics display	no
Redundancy function	yes
Note on redundancy function	applicative system redundancy, PN S2 (IO controller and IO device)
Safety function	no
Note on the safety function	Functional safety is provided with the left-alignable AXC F XT SPLC 1000 or AXC F XT SPLC 3000 extension modules.
Industrial cybersecurity	yes

Programming data

Register length (master)	1482 Byte

Functionality

Programming tool	PLCnext Engineer
	Eclipse®
	Visual Studio®
	MATLAB®/ Simulink®
Programming languages supported	Symbolic flowchart (SFC)
	Ladder diagram (LD)

	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
	Simulink®

System requirements

Application interface	OPC UA®

Electrical properties

Maximum power dissipation for nominal condition	5.6 W (5.6 W = 10.6 W - 5.0 W)

Real-time clock

Real-time clock	yes
Description real-time clock	typ. 10 ppm, max. 20 ppm at 25°C
Power reserve	120 h (at 25°C, from hardware version 07)
	240 h (at 25°C, to hardware version 06)

Potentials: Communications power U_L feed-in (the supply of the Axioline F local bus U_{Bus} is generated from U_L)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple (± 5 %))
Current draw	max. 442 mA (with 1 A at U_{Bus} for the I/Os)
Current consumption	typ. 200 mA (without I/Os and U_L = 24 V)
Power consumption	max. 10.6 W (with 1 A at U_{Bus} for the I/Os)
Protective circuit	Surge protection; electronic
	Reverse polarity protection; electronic

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
Power supply unit	1 A

Connection data

Axioline F connector

Connection method	Push-in connection
Conductor cross-section, rigid	0.2 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.2 mm² ... 1.5 mm²
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Interfaces

Supported protocols	HTTP
	HTTPS
	PROFINET

	INTERBUS
	Modbus/TCP (via corresponding library)
	Modbus/RTU (via corresponding library)
	EtherNet/IP™ FS Adapter)
	CANopen® (via corresponding library)
	DALI (via corresponding library)
	DALI-2 (via corresponding app)
	HART (via corresponding library)
	IO-Link® (via corresponding library)
	PROFIBUS
	MQTT (via corresponding app)
	OPC UA® Server
	OPC UA® Client (License required)
	DHCP (via corresponding library)
	SFTP
	SMTP (via corresponding library)
	SNTP (via corresponding library)
	SNMP (via corresponding library)
	DNS (via corresponding library)
	DNP3 (via corresponding library)
	IEC 60870-5-1 (via corresponding library)
	IEC 60870-5-104 (via corresponding library)
	IPsec
	syslog
Web server	yes

Axioline F local bus

Number of interfaces	1
Connection method	Bus base module
Transmission speed	100 Mbps


Ethernet

Bus system	RJ45
Number of interfaces	2 (Switched internally)
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps (full duplex)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	max. 100 m

Memory card:

Number	1 (SD card from Phoenix Contact (for external flash memory, see accessories))

Dimensions

Dimensional drawing	
Width	45 mm
Height	126.93 mm
Depth	75 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

Material specifications

Color (Housing)	gray (RAL 7042)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Manufacturers declaration, not evaluated by UL)
Ambient temperature (operation)	-25 °C ... 60 °C up to 2000 m above mean sea level (observe derating)
	-25 °C ... 55 °C up to 3000 m above mean sea level (observe derating)
	55 °C (with max. 1 A on U_{Bus})
	55 °C ... 60 °C (only in conjunction with an Axioline F power module AXL F PWR 1H (Item no. 2688297))
	-40 °C ... 70 °C (Extended, see Section “Tested successfully: use under extreme ambient conditions” in the user manual)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	5 % ... 95 % (according to DIN EN 61131-2)
Shock (operation)	30g (in accordance with EN 60068-2-27/IEC 60068-2-27)
Vibration (operation)	5g (in accordance with EN 60068-2-6/IEC 60068-2-6)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)

Approvals

ATEX

Identification	Ⓔx II 3 G Ex ec IIC T4 Gc
Certificate	TÜV 19 ATEX 8356 X

IECEx

Identification	Ex ec IIC T4 Gc
Certificate	IECEx TUR 19.0031X

CCC / China-Ex

Identification	Ex ec IIC T4 Gc
Certificate	

UL Ex, USA / Canada

Identification	Class I, Zone 2, AEx ec IIC T4 Gc
	Ex ec IIC T4 Gc X
Certificate	E366272

UL, USA/Canada

Identification	cULus
Certificate	E238705

EMC data


Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	Immunity test in accordance with EN IEC 61000-6-2 Electrostatic discharge (ESD)IEC 61000-4-2 Criterion B, ±6 kV contact discharge, ±8 kV air discharge
	Immunity test in accordance with EN IEC 61000-6-2 Electromagnetic fieldsIEC 61000-4-3 Criterion A, Field intensity: 10 V/m
	Immunity test in accordance with EN IEC 61000-6-2 Fast transients (burst)IEC 61000-4-4 Criterion B, ±2 kV
	Immunity test in accordance with EN IEC 61000-6-2 Transient overvoltage (surge)IEC 61000-4-5 Criterion B; DC supply lines: ±0.5 kV/±1.0 kV (symmetrical/asymmetrical), fieldbus cable shielding: ±1.0 kV
	Immunity test in accordance with EN IEC 61000-6-2 Conducted interferenceIEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN IEC 61000-6-3 Class B

Mounting

Mounting type	DIN rail mounting

Drawings

Dimensional drawing



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2404267

DNV GL
Approval ID: TAA00000DF

LR
Approval ID: LR2480202TA-02

BSH
Approval ID: 840c

RINA
Approval ID: ELE008423XG001

ABS
Approval ID: 23-2449604-PDA

PROFINET
Approval ID: Z13024

PROFINET
Approval ID: Z13024

cULus Listed
Approval ID: E238705

FS Thermoprocess
Approval ID: 968 INS 799.01 25

Cybersecurity Certificate
Approval ID: 968 CSP 1037.00 25

ABS
Approval ID: 23-2449604-PDA

BSH
Approval ID: 840c

DNV GL
Approval ID: TAA00000DF

RINA
Approval ID: ELE008423XG001

LR
Approval ID: LR2480202TA-02

cULus Listed
Approval ID: E238705

PROFINET
Approval ID: Z13146

PROFINET
Approval ID: Z13146

Cybersecurity Certificate
Approval ID: 968 CSP 1037.00 25

FS Thermoprocess
Approval ID: 968 INS 799.01 25

cULus Listed
Approval ID: E366272

CCC
Approval ID: 2021122304114448

IECEx
Approval ID: IECEx TUR 19.0031X

cULus Listed
Approval ID: E366272

CCC
Approval ID: 2021122304114448

ATEX
Approval ID: TUEV 19 ATEX 8356 X

Classifications

ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207

ETIM

ETIM 10.0	EC000236

UNSPSC

UNSPSC 21.0	32151700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	283ed987-a288-4b1a-afd1-cb06231c8f4d

EF3.1 Climate Change

CO2e kg	10.57 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com