

ILC 2050 BI-L - Controller

2404671

<https://www.phoenixcontact.com/us/products/2404671>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular Inline controller for automation applications in the fields of building technology, infrastructure, and energy technology. Equipped with two logically separated IP address interfaces each with 2 integrated Fast Ethernet ports. Configurable assignment of the Ethernet ports for the use of the Spanning Tree Protocol, daisy chain and redundant ring structures for optimum availability. 4 LAN, 2 USB, and 2 RS-485 interfaces are integrated. It enables the direct connection of LonMark TP/FT-10 networks. The data point connections can be extended with up to 63 Inline I/O modules.

Similar figure

Product description

The ILC 2050 BI-L is the central controller for the automation of buildings, infrastructure, and energy. The industrial design guarantees a high level of reliability and therefore also makes the ILC 2050 BI-L suitable for business-critical applications. It is equipped with four LAN, two USB, and two RS-485 interfaces. It enables the direct connection of LonMark TP/FT-10 networks. The controller can be extended with a wide range of Inline modules for digital and analog I/Os and for all widely used bus systems. The corresponding drivers ensure uniform interfaces, thus greatly simplifying system integration.

Your advantages

- Time-optimized engineering using the Niagara 4 framework
- Support for all the main communication protocols used in building infrastructure automation
- Direct connection of LonMark TP/FT-10 networks (in accordance with the CEA-709 standard)
- Planning, engineering, and visualization in the Java-based Niagara 4 framework
- Easy extension of the Niagara 4 framework with self-programmed functions

powered by

niagara
framework®

Commercial data

Item number	2404671
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR18
Product key	DRHAAA

ILC 2050 BI-L - Controller

2404671

<https://www.phoenixcontact.com/us/products/2404671>



GTIN	4055626933030
Weight per piece (including packing)	340 g
Weight per piece (excluding packing)	243 g
Customs tariff number	85371091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Controller
Product family	Inline-Controller
Installation location	indoor use
Installation location	Control cabinet

System properties

Retentive data storage	2 GByte (eMMC)
RAM	1024 Mbyte DDR3 SDRAM

IEC 61131 runtime system

Data storage system	2 GByte (eMMC)
---------------------	----------------

INTERBUS-Master

Amount of process data	max. 4096 bit (INTERBUS)
Amount of process data (INTERBUS input/output data max.)	max. 4096 bit (INTERBUS)
Number of local bus devices that can be connected	max. 63 (observe current consumption)
Number of devices with parameter channel	max. 16

Programming data

Register length (master)	512 Byte
--------------------------	----------

Functionality

Programming languages supported	Niagara Framework®
---------------------------------	--------------------

Electrical properties

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC
Max. current consumption	≤ 1.5 A
Typical current consumption	≤ 170 mA (at nominal voltage without local bus device)

Real-time clock

Realtime clock	Yes
----------------	-----

Potentials: 24 V supply U_{ILC}

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 1.5 A

ILC 2050 BI-L - Controller



2404671

<https://www.phoenixcontact.com/us/products/2404671>

	typ. 170 mA (without connected I/O terminal blocks)
Potentials: 7.5 V communications power U_L (potential jumper)	
Supply voltage	7.5 V DC $\pm 5\%$
Power supply	max. 2 A DC
Potentials: 24 V analog supply U_{ANA} (potential jumper)	
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 0.5 A DC
Potentials: Main circuit supply (U_M)	
Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$)
Potentials: Segment circuit supply (U_S)	
Supply voltage	24 V DC (via Inline connector)
Power supply	max. 8 A DC (sum of $U_M + U_S$)

Connection data

Inline connector	
Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Interfaces

Supported protocols	BACnet/IP
	BACnet MS/TP (only at COM1 and COM2)
	Modbus/TCP
	Modbus/RTU
	KNX IP
	DALI
	DALI-2
	LON IP
	EnOcean
	SMI
	MP-Bus
	SNMP
	M-Bus
	MQTT
OPC UA	
Simple OpenADR	

	LDAP
	SMS
	CSV
	oBIX
	Milestone Video Framework Interface
	LonMark TP/FT

Ethernet

Bus system	RJ45
Number of interfaces	4
Connection method	RJ45 jack
Transmission speed	10/100 Mbps
No. of channels	2
Bus system	RS-485
Number of interfaces	2

USB

Bus system	USB type A
Number of interfaces	1
Connection method	USB type A, socket

USB

Bus system	Mini-USB
Number of interfaces	1

microSD

Bus system	microSD
Number of interfaces	1 (Top)
Connection method	microSD slot

Dimensions

Width	80 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	0 % ... 75 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	0 % ... 75 % (according to DIN EN 61131-2)

ILC 2050 BI-L - Controller



2404671

<https://www.phoenixcontact.com/us/products/2404671>

Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 hPa ... 106 kPa (up to 3000 m above sea level)
GRP_Temperature class	T4
Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37	Sulfur dioxide (SO ₂) 10 ±0.3 ppm (test duration: 10 days), hydrogen sulfide (H ₂ S) 1 ±0.3 ppm (test duration: 4 days), both at 25°C and with 75% humidity

Mounting

Mounting type	DIN rail mounting
Mounting position	horizontal
	Alternative mounting positions are possible, but can lead to a reduction in thermal performance.

ILC 2050 BI-L - Controller

2404671

<https://www.phoenixcontact.com/us/products/2404671>



Classifications

ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

ILC 2050 BI-L - Controller



2404671

<https://www.phoenixcontact.com/us/products/2404671>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com