

# AXL F AI4 U 1H - Analog module

2688501

<https://www.phoenixcontact.com/us/products/2688501>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Analog input module, Analog inputs: 4, 0 V ... 5 V, -5 V ... 5 V, 0 V ... 10 V, -10 V ... 10 V, connection technology: 2-, 3-, 4-conductor, transmission speed in the local bus: 100 Mbps, integrated sensor supply, degree of protection: IP20, including bus base module and Axioline F connectors

## Product description

The module is designed for use within an Axioline F station. It is used to acquire analog voltage signals.

## Your advantages

- 4 analog, bipolar input channels for the connection of voltage signals
- Connection of sensors in 2-, 3-, and 4-conductor technology
- Voltage ranges: 0 V ... 10 V,  $\pm 10$  V, 0 V ... 5 V,  $\pm 5$  V
- Simultaneous scanning of all channels by means of simultaneous sampling
- High crosstalk attenuation between the channels, thanks to separate signal paths
- Particularly robust against electromagnetic interference
- Device rating plate stored

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2688501       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR02          |
| Product key                          | DRI241        |
| GTIN                                 | 4046356744232 |
| Weight per piece (including packing) | 197.4 g       |
| Weight per piece (excluding packing) | 191 g         |
| Customs tariff number                | 85389091      |
| Country of origin                    | DE            |


# AXL F AI4 U 1H - Analog module

2688501

<https://www.phoenixcontact.com/us/products/2688501>

## Technical data

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 35 mm  |
| Height              | 126.1 mm   |
| Depth               | 54 mm  |
| Note on dimensions  | The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715). |

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Material specifications

|                 |                 |
|-----------------|-----------------|
| Color (Housing) | gray (RAL 7042) |
|-----------------|-----------------|

### Interfaces

#### Axioline F local bus

|                      |                 |
|----------------------|-----------------|
| Number of interfaces | 2               |
| Connection method    | Bus base module |
| Transmission speed   | 100 Mbps        |

### System properties

#### Programming data (LocalbusSlave)

|                     |        |
|---------------------|--------|
| Input address area  | 8 Byte |
| Output address area | 0 Byte |

#### Fieldbus data telegram (PROFIBUS)

|                             |        |
|-----------------------------|--------|
| Required parameter data     | 7 Byte |
| Required configuration data | 6 Byte |

### Input data

#### Analog:

|                          |                              |
|--------------------------|------------------------------|
| Input name               | Analog inputs                |
| Description of the input | Differential inputs, voltage |
| Number of inputs         | 4                            |

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

|   |  |
|---|--|
| A/D conversion time                       | 31.25 µs   |
| Connection method                         | Push-in connection   |
| Connection technology                     | 2-, 3-, 4-conductor  |
| Note regarding the connection technology  | shielded, twisted pair   |
| Voltage input signal                      | 0 V ... 5 V  |
|   | -5 V ... 5 V   |
|   | 0 V ... 10 V   |
|   | -10 V ... 10 V   |
| Input resistance of voltage input         | 268 kΩ (typical)   |
| A/D converter resolution                  | 16 bit   |
| Data formats                              | IB IL, S7-compatible   |
| Input filter                              | 30 Hz, 12 kHz and mean value generation (can be parameterized) |
| Limit frequency (3 dB)                    | 30 Hz  |
|   | 12 kHz   |
| Common mode voltage range signal - ground | -50 V DC ... 50 V DC   |
| Measured value representation             | 16 bits (15 bits + sign bit)                                   |
| Protective circuit                        | Transient protection of inputs; Suppressor diode               |
|   | Overload protection of the inputs; ±30 V DC, maximum           |

## Product properties

|                    |   |
|--------------------|---|
| Product type       | I/O component                                       |
| Product family     | Axioline F  |
| Type               | block modular                                       |
| Mounting position  | any (no temperature derating)                       |
| Scope of supply    | including bus base module and Axioline F connectors |
| Special properties | integrated sensor supply                            |

## Insulation characteristics

|                      |                              |
|----------------------|------------------------------|
| Overvoltage category | II (IEC 60664-1, EN 60664-1) |
| Pollution degree     | 2 (IEC 60664-1, EN 60664-1)  |

## Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 1.85 W |
|---|--------|

### Potentials: Axioline F local bus supply ( $U_{Bus}$ )

|                |                              |
|----------------|------------------------------|
| Supply voltage | 5 V DC (via bus base module) |
| Current draw   | max. 150 mA (up to HW 03)    |
|                | max. 60 mA (from HW 04)      |
|                | typ. 120 mA (up to HW 03)    |
|                | typ. 53 mA (from HW 04)      |

### Potentials: Supply for analog modules ( $U_A$ )

|                      |   |
|----------------------|---|
| Supply voltage       | 24 V DC (I/O supply and sensor supply)  |
| Supply voltage range | 19.2 V DC ... 30 V DC (including all tolerances, including ripple)<br>max. 245 mA ( $I_{IS} = 4 \times 50$ mA (full load), up to HW 03) |

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

|                     |   |
|---------------------|---|
| Current draw        | max. 238 mA ( $I_{IS} = 4 \times 50$ mA (full load), from HW 04)  |
|                     | typ. 34 mA ( $I_{IS} = 0$ mA, from HW 04)   |
|                     | max. 45 mA ( $I_{IS} = 0$ mA, up to HW 03)  |
|                     | max. 38 mA ( $I_{IS} = 0$ mA, from HW 04)   |
|                     | typ. 238 mA ( $I_{IS} = 4 \times 50$ mA (full load), up to HW 03)   |
|                     | typ. 234 mA ( $I_{IS} = 4 \times 50$ mA (full load), from HW 04)  |
| Current consumption | typ. 38 mA ( $I_{IS} = 0$ mA, up to HW 03)  |
| Protective circuit  | Surge protection; electronic (35 V, 0.5 s)  |
|                     | Reverse polarity protection; up to HW 02: polarity protection diode from HW 03: parallel diode; with external 5 A fuse (for startup only) |
|                     | Transient protection; Suppressor diode  |

## Supply:

|                     |                          |
|---------------------|--------------------------|
| Designation         | Sensor supply $U_{IS}$   |
| Supply voltage      | 24 V DC (from $U_A$ )    |
| Current consumption | max. 50 mA (per channel) |

## Electrical isolation/isolation of the voltage ranges

|  |                        |
|--|------------------------|
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / 24 V supply (I/Os) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / analog inputs      | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / functional ground  | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / analog inputs                              | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / functional ground                          | 500 V AC, 50 Hz, 1 min |
| Test voltage: Analog inputs / functional ground                              | 500 V AC, 50 Hz, 1 min |

## Connection data

### Connection technology

|                               |   |
|-------------------------------|---|
| Connection name               | Axioline F connector  |
| Note on the connection method | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |

### Axioline F connector

|                                   |   |
|-----------------------------------|---|
| Connection method                 | Push-in connection  |
| Note on the connection method     | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |
| Conductor cross-section, rigid    | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section, flexible | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section AWG       | 24 ... 16   |
| Stripping length                  | 8 mm  |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 60 °C |
|---------------------------------|------------------|

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

|  |   |
|--|---|
| Degree of protection                     | IP20  |
| Air pressure (operation)                 | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Air pressure (storage/transport)         | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C                                  |
| Permissible humidity (operation)         | 5 % ... 95 % (non-condensing)                     |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing)                     |

## Mechanical test

|  |     |
|--|-----|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | 5g  |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27              | 30g |
| Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27   | 10g |

## Standards and regulations

|                  |                                       |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

## Mounting

|                   |                               |
|-------------------|-------------------------------|
| Mounting type     | DIN rail mounting             |
| Mounting position | any (no temperature derating) |

# AXL F AI4 U 1H - Analog module

2688501


<https://www.phoenixcontact.com/us/products/2688501>

## Drawings

Dimensional drawing



Connection diagram




Connector for voltage measurement

# AXL F AI4 U 1H - Analog module

2688501

<https://www.phoenixcontact.com/us/products/2688501>

Block diagram



Internal wiring of the terminal points

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2688501>



**DNV GL**

Approval ID: TAA00000DF



**LR**

Approval ID: LR2480202TA-02



**PRS**

Approval ID: TE/1020/880590/21

**BSH**

Approval ID: 840



**RINA**

Approval ID: ELE008423XG001

**ABS**

Approval ID: 23-2449604-PDA



**cULus Listed**

Approval ID: E238705

**ABS**

Approval ID: 23-2449604-PDA

**BSH**

Approval ID: 840



**DNV GL**

Approval ID: TAA00000DF



**PRS**

Approval ID: TE/1020/880590/21

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>



**RINA**

Approval ID: ELE008423XG001



**LR**

Approval ID: LR2480202TA-02



**cULus Listed**

Approval ID: E238705



**cULus Listed**

Approval ID: E238705

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242601 |
| ECLASS-15.0 | 27242601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001596 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

# AXL F AI4 U 1H - Analog module



2688501

<https://www.phoenixcontact.com/us/products/2688501>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)  |
|                                     | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP                                | a1def7f1-8886-4882-b885-3755a9763dab                        |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)