

FMC-IB IL TEMP 2 RTD-PAC - Inline function terminal



2696454

<https://www.phoenixcontact.com/us/products/2696454>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Product description

The terminal is designed for use within an Inline station. It is used to acquire signals from resistive temperature sensors. The terminal supports all common platinum and nickel sensors according to DIN EN 60751 and SAMA. Cu10, Cu50, and Cu53 sensors as well as KTY81 and KTY84 sensors are also supported. The measuring temperature is represented by 16-bit values in two process data words (one word per channel).

Commercial data

Item number	2696454
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI14X
GTIN	4046356327886
Weight per piece (including packing)	90 g
Weight per piece (excluding packing)	90 g
Customs tariff number	85389099
Country of origin	DE

FMC-IB IL TEMP 2 RTD-PAC - Inline function terminal



2696454

<https://www.phoenixcontact.com/us/products/2696454>

Technical data

Notes

Utilization restriction

EMC note

EMC: class A product, see manufacturer's declaration in the download area

Connection data

Stripping length

8 mm

FMC-IB IL TEMP 2 RTD-PAC - Inline function terminal



2696454

<https://www.phoenixcontact.com/us/products/2696454>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com