

# ILC 191 ME/INC - Controller



2700075

<https://www.phoenixcontact.com/us/products/2700075>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, fast counters, and incremental encoder inputs, with programming options according to IEC 61131-3

## Your advantages

- Web server, FTP server, and Flash file system
- Integrated fast counters and incremental encoder inputs
- Integrated pulse/direction/PWM interface
- Integrated RS-485/RS-422 interface
- Numerous protocols supported such as: HTTP, FTP, SNMP, SMTP, SQL, MySQL, etc.
- Modbus/TCP server
- Large program memory and data storage (1024 kB/1024 kB)
- Modbus/TCP-Client
- PROFINET-Device
- HTML 5
- Free engineering with PC Worx Express (IEC 61131-3)

## Commercial data

Item number	2700075
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR10
Product key	DRAAAA
GTIN	4046356479103
Weight per piece (including packing)	607.8 g
Weight per piece (excluding packing)	450 g
Customs tariff number	85371091
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Controller
Product family	Inline
Type	modular

#### Display

Diagnostics display	no
---------------------	----

### System properties

Retentive data storage	48 kByte (NVRAM)
------------------------	------------------

#### IEC 61131 runtime system

Program memory	1 Mbyte
Data storage system	1 Mbyte
Number of control tasks	8

#### INTERBUS-Master

Amount of process data	max. 4096 bit (INTERBUS)
Amount of process data (INTERBUS input/output data max.)	max. 4096 bit (INTERBUS)
Amount of process data (Modbus/TCP client)	max. 32768 bit (internal Modbus /TCP client)
Number of supported devices	max. 128
Number of local bus devices that can be connected	max. 63 (observe current consumption)
Number of devices with parameter channel	max. 24
Number of supported branch terminals with remote bus branch	max. 3

#### Modbus/TCP-Client

Amount of process data	max. 32768 bit (internal Modbus /TCP client)
Number of Modbus/TCP clients	max. 16 later than FW 4.42

#### PROFINET

Device function	PROFINET device
-----------------	-----------------

#### Function

Diagnostics display	no
Redundancy function	no
Safety function	no

#### Functionality

Programming languages supported	Programming in acc. with IEC 61131-3
---------------------------------	--------------------------------------

2700075

<https://www.phoenixcontact.com/us/products/2700075>

## System requirements

Configuration tool	Config+ Version 1.01 or later
Diagnostics tool	DIAG+
Runtime system	eCLR
Application interface	OPC

## Electrical properties

Transmission medium	Copper
Maximum power dissipation for nominal condition	max. 8.4 W

## Supply

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC
Residual ripple	± 5 %
Typical current consumption	350 mA

## Real-time clock

Realtime clock	yes
Description realtime clock	integrated (rechargeable battery buffered)

## Potentials

Supply voltage	7.5 V DC ±5 %
Power supply	max. 0.8 A DC (observe derating)

## Potentials

Supply voltage	24 V DC -15 % / +20 %
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	0.5 A DC (observe derating)

## Potentials

Supply voltage	24 V DC -15 % / +20 % (in accordance with EN 61131-2)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A DC (sum of $U_M + U_S$ )
Current draw	max. 8 A DC

## Potentials

Supply voltage	24 V DC -15 % / +20 % (in accordance with EN 61131-2)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A (sum of $U_M + U_S$ )
Current draw	max. 8 A DC

## Input data

### Encoder

Input name	Encoder input
Number of inputs	2 (3-coil, asymmetrical)
Input voltage range "1" signal	5 V DC ... 24 V DC

# ILC 191 ME/INC - Controller



2700075

<https://www.phoenixcontact.com/us/products/2700075>

## Digital:

Input name	Digital inputs
Description of the input	EN 61131-2 type 1 NPN/PNP
Number of inputs	8
Connection method	Inline potential distributor
Connection technology	2-, 3-, 4-conductor
Input voltage range	-0.5 V ... 30 V
Input voltage range "0" signal	-0.5 V ... 5 V
Input voltage range "1" signal	15 V ... 30 V
Typical response time	min. 3 ms

## Counter:

Input name	Counter input for 24 V signals
Number of inputs	2
Input voltage range "1" signal	5 V DC ... 24 V DC
Input frequency	200 kHz

## Output data

### Digital:

Output name	Digital outputs
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Number of outputs	4
Output voltage	24 V DC
Maximum output current per channel	500 mA

### Pulse direction

Output name	Pulse directional output for 5 V signals
Number of pulse direction outputs	2 (can be used as an alternative to pulse width modulation)
Output voltage	5 V
Limit frequency	150 kHz

## Connection data

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

## Interfaces

Web server	yes
------------	-----

### Ethernet 10Base-T/100Base-TX

Bus system	RJ45
------------	------

# ILC 191 ME/INC - Controller



2700075

<https://www.phoenixcontact.com/us/products/2700075>

Number of interfaces	2
Connection method	RJ45 jack
Transmission speed	10/100 Mbps

## INTERBUS local bus (master)

Number of interfaces	1
Connection method	Inline data jumper
Transmission speed	500 kBaud / 2 MBaud (can be switched)

## Parameterization/operation/diagnostics

Bus system	RS-232
Number of interfaces	1
Connection method	6-pos. MINI DIN socket (PS/2)
Transmission speed	max. 115.2 kbps
Transmission physics	Copper
No. of channels	1

## RS-422/-485

Bus system	RS-485/-422
Number of interfaces	1
Connection method	4-pos. for full duplex 2-pos. for half duplex

## Dimensions

Width	164 mm
Height	136.8 mm
Depth	71.5 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (operation)	5g
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

# ILC 191 ME/INC - Controller



2700075

<https://www.phoenixcontact.com/us/products/2700075>

Conformance with EMC directives	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Electrostatic discharge (ESD)EN 61000-4-2/IEC 61000-4-2 Criterion B, $\pm 6$ kV contact discharge, $\pm 8$ kV air discharge
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Electromagnetic fieldsEN 61000-4-3/IEC 61000-4-3 Criterion A, Field intensity: 10 V/m
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Fast transients (burst)EN 61000-4-4/IEC 61000-4-4 Criterion A, all interfaces $\pm 1$ kVCriterion B, all interfaces $\pm 2$ kV
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Transient overvoltage (surge)EN 61000-4-5/IEC 61000-4-5 Criterion B, supply lines DC: 0.5 kV/0.5 kV (symmetrical/asymmetrical), fieldbus cable shield 1 kV
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Conducted interferenceEN 61000-4-6/IEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN 61000-6-4/IEC 61000-6-4 EN 55011 Class A

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# ILC 191 ME/INC - Controller

2700075

<https://www.phoenixcontact.com/us/products/2700075>



## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)