

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Smart Managed Narrow switch with six 10/100 Mbps RJ45 ports und two 100 Mbps POF SC-RJ ports, PROFINET mode (default)

## Product description

The Smart Managed Narrow switch (SMN) is an industrial Ethernet switch with six Fast Ethernet ports in RJ45 format and two fiber optic ports in POF format. (FL SWITCH SMN 6TX/2POF-PN) By default upon delivery the switch operates in "PROFINET" mode.

## Your advantages

- PROFINET-Device
- SNMP
- MRP (client and manager)
- VLANs
- RSTP
- Web-based management, SNMP
- Slim design

## Commercial data

Item number	2700290
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN17
Product key	DNN122
GTIN	4046356525954
Weight per piece (including packing)	845.8 g
Weight per piece (excluding packing)	720 g
Customs tariff number	85176200
Country of origin	DE

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

## Technical data

### Dimensions

Width	57 mm
Height	133 mm
Depth	125 mm

### Material specifications

Color	gray aluminum
-------	---------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

#### Ethernet

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	6 (RJ45 ports)

#### POF/PCF

Connection method	POF SC-RJ
Transmission speed	10/100 Mbps (full duplex)
Transmission physics	POF-SCRJ
Transmission length	up to 100 m (depending on the fiber used)
Wavelength	650 nm
No. of channels	2 (SC-RJ)

#### Serial (RS-232)

Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)
-------------------	---

### Product properties

Product type	Switch
Product family	Managed Switch SMN
Type	Book type

#### Switch functions

Diagnostic functions	RMON History
	N:1-Portmirroring
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

	classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
Signal contact control voltage	24 V (typical)
Signal contact control current	100 mA
PROFINET conformance class	Conformance Class B
PROFINET device function	PROFINET device
	Fast Startup
Filter functions	Quality of Service (4 priority classes)
	Port-Priorisierung
	VLAN
	IGMP Snooping (128 groups)
	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
	Static Multicast Filtering
Management	Web-based management (HTTP)
	SNMP v1/v2
	Serial interface (V.24)
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	FRD (Fast Ring Detection)
	Large Tree Support
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
Supported browsers	Internet Explorer 5.5 or higher
Additional functions	BootP
	DHCP-Client
Time synchronization	SNTP

## Security functions

Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2

## Electrical properties

Current consumption	320 mA
Local diagnostics	US1/2 Supply voltage US1, US2 Green LED
	FAIL Div. LED red
	LNK/ACT Link status Green LED
	ACT/MODE Receiving/sending telegrams Green LED
	SPD/MODE Data transmission speed Green LED
	FD/FO Duplex mode with twisted pair ports; system reserve of

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

	the POF-SCRJ interface Green LED
Maximum power dissipation for nominal condition	7.68 W
Transmission medium	Copper
	FO

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	18 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Typical current consumption	340 mA (at U <sub>S</sub> = 24 V DC)
Current consumption	320 mA

## Function

Signal contact control voltage	24 V (typical)
Signal contact control current	100 mA

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (2000 m above mean sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

## Standards and regulations

Free from substances that could impair the application of coating	Yes
---	-----

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion A
	IEC 61000-4-3 (electromagnetic fields) Criterion A
	IEC 61000-4-4 (burst) Criterion A
	IEC 61000-4-5 (surge) Criterion A
	IEC 61000-4-6 (immunity to conducted interference) Criterion A

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

Noise immunity	EN 61000-6-2:2005
Noise emission	
Standards/regulations	EN 61000-6-4:2007 + A1:2011

## System properties

### Functionality

Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
-----------------	--

### System requirements

Supported browsers	Internet Explorer 5.5 or higher
--------------------	---------------------------------

## Signaling

Status display	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
----------------	---

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

## Classifications

### UNSPSC

UNSPSC 21.0	43222612
-------------	----------

# FL SWITCH SMN 6TX/2POF-PN - Industrial Ethernet Switch



2700290

<https://www.phoenixcontact.com/us/products/2700290>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)