

FLK 16/14/DV-IN/400 - Cable



2305185

<https://www.phoenixcontact.com/us/products/2305185>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; controller: Emerson Delta V; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

Your advantages

- The DeltaV system can be used to install the process wiring via "mass termination blocks" (MTBs) using flat-ribbon cable plugs
- For digital modules with 16-pos. MTB for connection to PLC-INTERFACE

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2305185 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK221K |
| GTIN | 4046356038904 |
| Weight per piece (including packing) | 243.5 g |
| Weight per piece (excluding packing) | 243.5 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

FLK 16/14/DV-IN/400 - Cable



2305185

<https://www.phoenixcontact.com/us/products/2305185>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|----------------------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating) |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

Supported controller: EMERSON DeltaV

| | |
|-------------------|--------------|
| Suitable I/O card | VE4001S2T1B3 |
| | VE4001S2T2B3 |

Cable/line

| | |
|--------------|-----|
| Cable length | 4 m |
|--------------|-----|

16X0.14 [PVC]

| | |
|---------------------------------|--------------------------|
| UL AWM Style | 2464/1061 |
| Number of positions | 16 |
| Shielded | no |
| Cable type | 16X0.14 [PVC] |
| Conductor type | Round cable set |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 16x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 6.80 mm ±0.4 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |

FLK 16/14/DV-IN/400 - Cable



2305185

<https://www.phoenixcontact.com/us/products/2305185>

| | |
|---|--|
| Smallest bending radius, fixed installation | 58 mm |
| Smallest bending radius, movable installation | 108 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of $\geq 15x$ outside diameter) |
| Halogen-free | no |
| Flame resistance | IEC 60332-1-2 (raw cable) |
| | VDE 0842, Part 332-1-2 (raw cable) |
| | IEC 60332-3-22 (raw cable) |
| | UL VW-1 |
| | CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Cable for one module |

Color code: Single-core wire

| | |
|--------------|---------------------------------|
| black | IDC/FLK16 (1) = IDC/FLK14 (1) |
| brown | IDC/FLK16 (2) = IDC/FLK14 (9) |
| red | IDC/FLK16 (3) = IDC/FLK14 (2) |
| orange | IDC/FLK16 (4) = IDC/FLK14 (9) |
| yellow | IDC/FLK16 (5) = IDC/FLK14 (3) |
| green | IDC/FLK16 (6) = IDC/FLK14 (9) |
| blue | IDC/FLK16 (7) = IDC/FLK14 (4) |
| violet | IDC/FLK16 (8) = IDC/FLK14 (11) |
| gray | IDC/FLK16 (9) = IDC/FLK14 (5) |
| white | IDC/FLK16 (10) = IDC/FLK14 (11) |
| white-black | IDC/FLK16 (11) = IDC/FLK14 (6) |
| white-brown | IDC/FLK16 (12) = IDC/FLK14 (11) |
| white-red | IDC/FLK16 (13) = IDC/FLK14 (7) |
| white-orange | IDC/FLK16 (14) = IDC/FLK14 (13) |
| white-yellow | IDC/FLK16 (15) = IDC/FLK14 (8) |
| white-green | IDC/FLK16 (16) = IDC/FLK14 (13) |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 16 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 14 |

FLK 16/14/DV-IN/400 - Cable



2305185

<https://www.phoenixcontact.com/us/products/2305185>

| | |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Diagram



Maximum permissible current per path in uncoiled state

FLK 16/14/DV-IN/400 - Cable

2305185

<https://www.phoenixcontact.com/us/products/2305185>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

FLK 16/14/DV-IN/400 - Cable



2305185

<https://www.phoenixcontact.com/us/products/2305185>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com