

# RAD-ISM-2459-ANT-FOOD-6-0-MCX - Antenna



2700674

<https://www.phoenixcontact.com/us/products/2700674>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Dual band omnidirectional antenna with protection against vandalism; IP68 protection; frequency band/gain: 2.4 GHz/up to 6 dBi, 5 GHz/up to 8 dBi; EN 50155; temperature range: -40°C to +80°C; N (f) connection; 1 m long adapter cable, N (m) - MCX (m) connection.

## Commercial data

Item number	2700674
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356617581
Weight per piece (including packing)	280.1 g
Weight per piece (excluding packing)	280.1 g
Customs tariff number	85177011
Country of origin	CH

2700674

<https://www.phoenixcontact.com/us/products/2700674>

## Technical data

### Product properties

Product type	Antenna
Gain	6 dBi (2.4 GHz, when mounted on metal surface)
	3 dBi (2.4 GHz, no metal surface)
	8 dBi (5.6 GHz, when mounted on metal surface)
	5 dBi (5.6 GHz, no metal surface)
Horizontal beamwidth	360 °

### Electrical properties

Frequency band	2.4 GHz
	5 GHz
Frequency range	2.4 GHz
	5.15 GHz ... 5.83 GHz
Impedance	50 Ω

### Connection data

#### Connection technology

Connection method	N (female)
-------------------	------------

### Dimensions

Height	51 mm
Diameter	92 mm

### Material specifications

Housing material	Aluminum, HRA 150
Outer sheath, material	RADOX®(LSFH)

### Cable/line

Cable length	1.00 m
Connecting cable	yes
Cable type	EF 316
External cable diameter	2.50 mm
Outer sheath, material	RADOX®(LSFH)
Bending radius, long-term	12.50 mm

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Wind velocity	12.34568 km/h (Has a force of 10 N)

# RAD-ISM-2459-ANT-FOOD-6-0-MCX - Antenna



2700674

<https://www.phoenixcontact.com/us/products/2700674>

## Mounting

Mounting type	Control cabinet
Assembly note	Protection class: IP68, only when mounted on a level surface

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)